



75 Ohm 2 Way BNC Power Divider From
2 MHz to 500 MHz Rated at 1 Watts

TECHNICAL DATA SHEET

PE2048

75 Ohm 2 Way BNC Power Divider From 2 MHz to 500 MHz Rated at 1 Watts

Configuration

Input Connector	BNC Female
Output Connectors	BNC Female
Frequency Range, MHz	2 to 500
Number of Output Ports	2

Electrical Specifications

Frequency Range, MHz	2 to 500
Impedance, Ohms	75
Maximum Insertion Loss, dB	1
Maximum Input Power, Watts	1
Maximum Input VSWR	1.35:1
Minimum Isolation, dB	25
Phase Balance, Degrees	± 2

Mechanical Specifications

Size

Length, in [mm]	1.67 [42.42]
Width, in [mm]	2.8 [71.12]
Height, in [mm]	0.93 [23.62]

Compliance Certifications (visit www.Pasternack.com for current document)

Plotted and Other Data

Notes: Values at 25 °C, sea level

75 Ohm 2 Way BNC Power Divider From 2 MHz to 500 MHz Rated at 1 Watts from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [75 Ohm 2 Way BNC Power Divider From 2 MHz to 500 MHz Rated at 1 Watts PE2048](http://www.pasternack.com/2-way-bnc-reactive-power-divider-2-mhz-500-mhz-1-watts-pe2048-p.aspx)

URL: <http://www.pasternack.com/2-way-bnc-reactive-power-divider-2-mhz-500-mhz-1-watts-pe2048-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

PE2048 CAD Drawing

75 Ohm 2 Way BNC Power Divider From 2 MHz to 500 MHz Rated at 1 Watts



NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE
PE2048

REV. A | FSCM NO. 53919

127

SIZE A

SCALE N/A

CAD FILE 031010-A

PE PASTERNAK
 Pasternack Enterprises, Inc.
 P.O. Box 16759 | Irvine | CA | 92623
 Phone: (949) 261-1920 | Fax: (949) 261-7451
 Website: www.pasternack.com | E-Mail: sales@pasternack.com