


| COMPONENTS | IMPEDANCE |
|------------|-----------|
| 7/16 MALE | 50 OHM |
| 7/16 MALE | 50 OHM |
| RG223/U | 50 OHM |
| | |

| Standard Lengths | |
|------------------|-------------------------|
| -12 | 12" |
| -24 | 24" |
| -36 | 36" |
| -48 | 48" |
| -60 | 60" |
| -XXX | Custom Length in inches |
| | |



PASTERNACK ENTERPRISES, INC.
P.O BOX 16759, IRVINE, CA 92623
PHONE (949) 261-1920 FAX (949) 261-7451
WEB ADDRESS: www.pasternack.com
E-MAIL ADDRESS: sales@pasternack.com
COAXIAL & FIBER OPTICS

| | | | | |
|-------------------------------|----------------|--|-----------|-----|
| DWG TITLE PE3192-XX | | DES. CABLE ASSEMBLY, RG223/U, 7/16 MALE TO 7/16 MALE | | |
| SIZE A | FSCM NO. 53919 | CAD FILE 030607 | SCALE N/A | 127 |

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES.
4. LENGTH TOLERANCE IS $\pm 1.5\%$ OR $\pm 3/8"$, WHICHEVER IS GREATER.