
COMPONENTS	IMPEDANCE
BNC MALE RIGHT ANGLE	50 OHM
BNC MALE RIGHT ANGLE	50 OHM
RG179B/U	75 OHM

Standard Lengths	
-12	12"
-24	24"
-36	36"
-48	48"
-60	60"
-XXX	Custom Length in inches







PASTERNACK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623 PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE PE3366LF-XX CABLE ASSEMBLY, RG179B/U, BNC MALE RIGHT ANGLE TO BNC MALE RIGHT ANGLE (LEAD FREE)

FSCM NO. 53919 REV. A

CAD FILE 021308

SCALE N/A

SIZE A 147

NOTES:

- 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
- 3. DIMENSIONS ARE IN INCHES.
- 4. LENGTH TOLERANCE IS ± 1.5% OR ±3/8", WHICHEVER IS GREATER.