
COMPONENTS	IMPEDANCE
7/16 MALE	50 OHM
7/16 MALE	50 OHM
RG400/U	50 OHM

Standard Lengths		
-12	12"	
-24	24"	
-36	36"	
-48	48"	
-60	60"	
-XXX	Custom Length in inches	





RoHS Compliance Certified



PASTERNACK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623 PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE **PE34360LF-XX**

CABLE ASSEMBLY, RG400/U, 7/16 MALE TO 7/16 MALE (LEAD FREE)

FSCM NO. 53919 REV. A

CAD FILE 013008

SCALE N/A

SIZE A 147

- NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
- 3. DIMENSIONS ARE IN INCHES.
- 4. LENGTH TOLERANCE IS ± 1.5% OR ± 3/8", WHICHEVER IS GREATER.