
| COMPONENTS | IMPEDANCE |
|-------------|-----------|
| 2.92mm MALE | 50 OHM |
| 2.92mm MALE | 50 OHM |
| PE-SR405FL | 50 OHM |
| | |

| Standard Lengths | |
|------------------|-------------------------|
| -12 | 12" |
| -24 | 24" |
| -36 | 36" |
| -48 | 48" |
| -60 | 60" |
| -XXX | Custom Length in inches |
| | |





RoHS Compliance Certified



PASTERNACK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623 PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE **PE34737LF-XX**

CABLE ASSEMBLY, PE-SR405FL, 2.92mm MALE TO 2.92mm MALE (LEAD FREE)

FSCM NO. 53919 REV. A

CAD FILE 020508

SCALE N/A SIZE A

147

NOTES:

- UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
- 3. DIMENSIONS ARE IN INCHES.
- 4. LENGTH TOLERANCE IS ± 1.5% OR ± 3/8", WHICHEVER IS GREATER.