

10-32 Female Bulkhead Mount Connector Clamp/Solder Attachment for RG178, RG196, .295 inch D Hole



RF Connectors Technical Data Sheet

PE44368

Configuration

- 10-32 Female Connector
- MIL-C-39012
- 50 Ohms
- Straight Body Geometry

Features

• Gold Plated Contact

Applications

- General Purpose Test
- Rack and Panel Mount Applications
 Cus

Bulkhead

• RG178, RG196 Interface Type

Contact plating according to MIL-G-45204

Clamp/Solder Attachment

Custom Cable Assemblies

Description

Pasternack's PE44368 10-32 female bulkhead connector with clamp/solder attachment for RG178 and RG196 (.295 inch D hole) is part of our full line of RF components available for same-day shipping. This 10-32 bulkhead connector allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Our 10-32 female bulkhead connector PE44368 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

Mechanical Specifications

Size	
Length	0.72 in [18.29 mm]
Width/Dia.	0.438 in [11.13 mm]
Weight	0.016 lbs [7.26 g]

Material Specifications

Description	Material	Plating
Contact		Gold MIL-G-45204
Body	Brass	Nickel QQ-N-290

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 10-32 Female Bulkhead Mount Connector Clamp/Solder Attachment for RG178, RG196, .295 inch D Hole PE44368

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



Contraction of the second seco

10-32 Female Bulkhead Mount Connector Clamp/Solder Attachment for RG178, RG196, .295 inch D Hole

RF Connectors Technical Data Sheet

PE44368

Compliance Certifications (see product page for current document)

Plotted and Other Data Notes:

10-32 Female Bulkhead Mount Connector Clamp/Solder Attachment for RG178, RG196, .295 inch D Hole from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 10-32 Female Bulkhead Mount Connector Clamp/Solder Attachment for RG178, RG196, .295 inch D Hole PE44368

URL: https://www.pasternack.com/10-32-female-standard-rg178-rg196-connector-pe44368-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE44368 CAD Drawing 10-32 Female Bulkhead Mount Connector Clamp/Solder

Attachment for RG178, RG196, .295 inch D Hole

