



SMP Male Limited Detent Shroud 2 Hole
Flange Mount 0.282 Inch Hole Spacing

TECHNICAL DATA SHEET

PE44951

Configuration

| | |
|------------------------------------|--------------------------|
| Connector | SMP Male, Limited Detent |
| Connector Specification | DESC 94007 |
| Connector Interface Type | None |
| Attachment Method (Shield/Contact) | None |
| Body Style | Straight |
| Mount Method | 2 Hole Flange |

Electrical Specifications

| | |
|-----------|---------|
| Impedance | 50 Ohms |
|-----------|---------|

Mechanical Specifications

Size

| | |
|------------|---------------------|
| Length | 0.4 in [10.16 mm] |
| Width/Dia. | 0.165 in [4.19 mm] |
| Height | 0.12 in [3.05 mm] |
| Weight | 0.082 lbs [37.19 g] |

Connector

| | |
|----------------------------|----------------------------|
| Type | SMP Male |
| Body Material and Plating | Passivated Stainless Steel |
| Body Plating Specification | QQ-P-35 |

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMP Male Limited Detent Shroud 2 Hole Flange Mount 0.282 Inch Hole Spacing PE44951](#)



SMP Male Limited Detent Shroud 2 Hole
Flange Mount 0.282 Inch Hole Spacing

TECHNICAL DATA SHEET

PE44951

Plotted and Other Data

Notes:

- Values at +25 °C, sea level

SMP Male Limited Detent Shroud 2 Hole Flange Mount 0.282 Inch Hole Spacing from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMP Male Limited Detent Shroud 2 Hole Flange Mount 0.282 Inch Hole Spacing PE44951](#)

URL: <http://www.pasternack.com/smp-male-standard-shroud-pe44951-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE44951 CAD Drawing

SMP Male Limited Detent Shroud 2 Hole Flange Mount 0.282 Inch Hole Spacing



NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE
PE44951

FSCM NO. 53919

CAD FILE 110413

SCALE N/A

SIZE A

150

PE PASTERNAK®
 Pasternack Enterprises, Inc.
 P.O. Box 16759 | Irvine | CA | 92623
 Phone: (949) 261-1920 | Fax: (949) 261-7451
 Website: www.pasternack.com | E-Mail: sales@pasternack.com