



RP SMA Female Bulkhead Connector Solder Attachment
 Solder Cup Terminal, .235 inch D Hole, .150 inch Max Panel

TECHNICAL DATA SHEET

PE4868

RP SMA Female Bulkhead Connector Solder Attachment Solder Cup Terminal, .235 inch D Hole, .150 inch Max Panel

Configuration

Connector	SMA Female Reverse Polarity
Connector Interface Type	Solder Cup
Cable Attachment Method (Shield/Contact)	Solder
Body Style	Straight
Mount Method	Bulkhead

Electrical Specifications

Impedance, Ohms	50
-----------------	----

Mechanical Specifications

Size

Length, in [mm]	0.685 [17.4]
Width/Dia., in [mm]	0.312 [7.92]
Weight, lbs [g]	0.006 [2.72]

Connector

Type	SMA Female Reverse Polarity
Contact Material and Plating	Gold
Body Material and Plating	Stainless Steel, Gold
Dielectric Type	PTFE

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant	Yes
----------------	-----

Plotted and Other Data

Notes:	Values at 25 °C, sea level
--------	----------------------------

RP SMA Female Bulkhead Connector Solder Attachment Solder Cup Terminal, .235 inch D Hole, .150 inch Max Panel from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [RP SMA Female Bulkhead Connector Solder Attachment Solder Cup Terminal, .235 inch D Hole, .150 inch Max Panel PE4868](http://www.pasternack.com/sma-female-reverse-polarity-solder-cup-terminal-connector-pe4868-p.aspx)

URL: <http://www.pasternack.com/sma-female-reverse-polarity-solder-cup-terminal-connector-pe4868-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

PE4868 CAD Drawing

RP SMA Female Bulkhead Connector Solder Attachment Solder Cup Terminal, .235 inch D Hole, .150 inch Max Panel



NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE
PE4868

FSCM NO. 53919

XXXX

SIZE A

SCALE N/A

CAD FILE 061202

PE PASTERNAK®
 Pasternack Enterprises, Inc.
 P.O. Box 16759 | Irvine | CA | 92623
 Phone: (949) 261-1920 | Fax: (949) 261-7451
 Website: www.pasternack.com | E-Mail: sales@pasternack.com