

Product Features

- Wideband Vertical Antenna
- 2400-2500 MHz
- 150W power handling
- 3 dBi Gain

Specifications ⁽¹⁾

Parameter	Value	Units	Description
Minimum Frequency	2400	MHz	
Maximum Frequency	2500	MHz	
Gain	3	dBi	Max Gain
Polarization	Vert		Vertical Polarization
Max Input Pwr	150	W	Watts(Max)
Length	86.36	mm	3.4 Inches
Diameter	38.10	mm	1.5 Inches
Whip Material			Plastic Radome
Color			Black/Chrome
Mount Type			Order NMO Mount Separately



Ordering Information

Part Number	Description
PE51136	Low Profile Vertical Antenna, 2400-2500 MHz, Black/chrome, NMO Mount Type

(1) Pasternack reserves the right to change specifications or information without notice.

(2) All specifications "typical"