



3 dB Fixed Attenuator, BNC Male To BNC Female  
Directional Aluminum Heatsink Black Anodized  
Body Rated To 100 Watts Up To 1 GHz

TECHNICAL DATA SHEET

PE7026-3

**3 dB Fixed Attenuator, BNC Male To BNC Female Directional Aluminum Heatsink Black Anodized Body Rated To 100 Watts Up To 1 GHz**

**Configuration**

Design	Fixed, Directional Attenuator
Connector 1	BNC Male
Connector 2	BNC Female
Body Material and Plating	Aluminum Heatsink, Black Anodized

**Electrical Specifications**

Frequency Range, MHz	DC to 1,000
Impedance, Ohms	50
Attenuation Value, dB	3
Maximum Input Power, Watts	100
Maximum VSWR	1.4:1

**Frequency 1**

Range, MHz	DC to 1,000
VSWR	1.4:1
Attenuation Accuracy, dB	± 0.5

**Mechanical Specifications**

**Size**

Length, in [mm]	6.56 [166.62]
Width, in [mm]	3.46 [87.88]
Height, in [mm]	3.46 [87.88]

**Connector 1**

Type	BNC Male
Connector Specification	MIL-STD-348

**Connector 2**

Type	BNC Female
Connector Specification	MIL-STD-348

**Compliance Certifications** (visit [www.Pasternack.com](http://www.Pasternack.com) for current document)

RoHS Compliant	Yes
----------------	-----

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [3 dB Fixed Attenuator, BNC Male To BNC Female Directional Aluminum Heatsink Black Anodized Body Rated To 100 Watts Up To 1 GHz PE7026-3](#)

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.



3 dB Fixed Attenuator, BNC Male To BNC Female  
Directional Aluminum Heatsink Black Anodized  
Body Rated To 100 Watts Up To 1 GHz

TECHNICAL DATA SHEET

PE7026-3

**Plotted and Other Data**

Notes:

Values at 25 °C, sea level

3 dB Fixed Attenuator, BNC Male To BNC Female Directional Aluminum Heatsink Black Anodized Body Rated To 100 Watts Up To 1 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [3 dB Fixed Attenuator, BNC Male To BNC Female Directional Aluminum Heatsink Black Anodized Body Rated To 100 Watts Up To 1 GHz PE7026-3](http://www.pasternack.com/3db-fixed-bnc-female-bnc-male-100-watts-attenuator-pe7026-3-p.aspx)

URL: <http://www.pasternack.com/3db-fixed-bnc-female-bnc-male-100-watts-attenuator-pe7026-3-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

# PE7026-3 CAD Drawing

3 dB Fixed Attenuator, BNC Male To BNC Female Directional Aluminum Heatsink Black Anodized Body Rated To 100 Watts Up To 1 GHz

P/N	ATTEN.	FIGURE
PE7026-3	3 dB	1
PE7026-6	6 dB	1
PE7026-10	10 dB	1
PE7026-20	20 dB	1
PE7026-30	30 dB	1
PE7026-40	40 dB	1




FIGURE 1

DWG TITLE

**PE7026**

NOTES:  
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
 3. DIMENSIONS ARE IN INCHES [mm].

**PE PASTERNAK®**  
 Pasternack Enterprises, Inc.  
 P.O. Box 16759 | Irvine | CA | 92623  
 Phone: (949) 261-1920 | Fax: (949) 261-7451  
 Website: www.pasternack.com | E-Mail: sales@pasternack.com

FSCM NO. 53919

CAD FILE 022613

SCALE N/A

SIZE A

2231