



Banana Plug to Banana Plug Cable 72
Inch Length Using Red Wire

TECHNICAL DATA SHEET

PE9930-72-R

Banana Plug to Banana Plug Cable 72 Inch Length Using Red Wire

Configuration

Connector 1	Banana Plug
Connector 2	Banana Plug
Cable Type	Red Wire

Mechanical Specifications

Cable Assembly

Cable Type	Red Wire
------------	----------

Size

Length, in [cm]	72 [182.88]
Diameter, in [mm]	0.15 [3.81]
Weight, lbs [g]	0.017 [7.71]
Cable Color	Red

Cable

Jacket Material	Rubber
Jacket Diameter, in [mm]	0.15 [3.81]

Connector 1

Type	Banana Plug
Configuration	Straight

Connector 2

Type	Banana Plug
Configuration	Straight

Compliance Certifications (visit www.Pasternack.com for current document)

Plotted and Other Data

Notes: Values at 25 °C, sea level

Banana Plug to Banana Plug Cable 72 Inch Length Using Red Wire from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Banana Plug to Banana Plug Cable 72 Inch Length Using Red Wire PE9930-72-R](http://www.pasternack.com/banana-plug-to-banana-plug-cable-72-inch-length-using-red-wire-pe9930-72-r)


URL: <http://www.pasternack.com/banana-plug-banana-plug-red-wire-cable-assembly-pe9930-72-r-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

PE9930-72-R CAD Drawing

Banana Plug to Banana Plug Cable 72 Inch Length Using Red Wire

Standard Lengths	
-6	6"
-9	9"
-12	12"
-18	18"
-24	24"
-XXX	Custom Length in Inches



- NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES (mm).
 4. LENGTH TOLERANCE IS $\pm 1.5\%$ OR $3/8"$, WHICHEVER IS GREATER.

DWG TITLE
PE9930-XX

PASTERNAK ENTERPRISES, INC.
 P.O. BOX 16759, IRVINE, CA 92623
 PHONE (949) 261-1920 FAX (949) 261-7451
 WEB ADDRESS: www.pasternack.com
 E-MAIL ADDRESS: sales@pasternack.com
COAXIAL & FIBER OPTICS



REV. -	FSCM NO. 53919	CAD FILE 021507	SCALE N/A	SIZE A	127
--------	----------------	-----------------	-----------	--------	-----