

WR-22 90 Degree Waveguide Twist With a UG-383/U Flange Operating From 33 GHz to 50 GHz

# Waveguide Twists Technical Data Sheet

VE WEETWING 150

## **PE-W22TW1001**

# Features WR-22 33 to 50 GHz UG-383/U Flange Applications

- InstrumentationPrecision measurements
- Prototyping and characterization
- Production Systems

### Description

The PE-W22TW1001 is a 90 degree waveguide twist that is part of a family of precision manufactured twists with round flange per MIL-DTL-85. The family includes right and left hand 45 degree twists as well as 90 degree twists. These twists are offered in the Ka through W waveguide bands (18 to 110 GHz).

### **Electrical Specifications**

33		50	GHz
		1.02:1	
		0.5	dB
	33	33	1.02:1

### **Electrical Specification Notes:**

VSWR measurement is the representation of the load used for testing

### **Mechanical Specifications**

Waveguide Size Section Length		WR-22 2 in [[50.8 mm]]	
Description	Flange 1	Waveguide	Flange 2
nterface	UG-383/U	WR-22	UG-383/U
Material	Brass	Brass	Brass
Plating	Gold	Gold	Gold
Color	Gold	Gold	Gold

### **Environmental Specifications**

Compliance Certifications (see product page for current document)

### **Plotted and Other Data**

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: WR-22 90 Degree Waveguide Twist With a UG-383/U Flange Operating From 33 GHz to 50 GHz PE-W22TW1001

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com






WR-22 90 Degree Waveguide Twist With a UG-383/U Flange Operating From 33 GHz to 50 GHz

# Waveguide Twists Technical Data Sheet

# **PE-W22TW1001**



WR-22 90 Degree Waveguide Twist With a UG-383/U Flange Operating From 33 GHz to 50 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: WR-22 90 Degree Waveguide Twist With a UG-383/U Flange Operating From 33 GHz to 50 GHz PE-W22TW1001

URL: https://www.pasternack.com/wr-22-90-waveguide-twist-ug383-33-50-ghz-pe-w22tw1001-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

# PE-W22TW1001 CAD Drawing

WR-22 90 Degree Waveguide Twist With a UG-383/U Flange Operating From 33 GHz to 50 GHz

