



SSMB Jack Bulkhead Connector Solder Attachment Turret Terminal, .126 inch D Hole, Rear Mount

TECHNICAL DATA SHEET

PE4338

SSMB Jack Bulkhead Connector Solder Attachment Turret Terminal, .126 inch D Hole, Rear Mount

Configuration

Connector	SSMB Jack
Connector Interface Type	Turret
Cable Attachment Method (Shield/Contact)	Solder
Body Style	Straight
Mount Method	Bulkhead

Electrical Specifications

Impedance, Ohms	50
-----------------	----

Mechanical Specifications

Size

Length, in [mm]	0.51 [12.95]
Width/Dia., in [mm]	0.156 [3.96]
Weight, lbs [g]	0.002 [0.91]

Connector

Type	SSMB Jack
Contact Material and Plating	Gold
Body Material and Plating	Brass, Gold
Dielectric Type	PTFE

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant	Yes
----------------	-----

Plotted and Other Data

Notes:	Values at 25 °C, sea level
--------	----------------------------

SSMB Jack Bulkhead Connector Solder Attachment Turret Terminal, .126 inch D Hole, Rear Mount from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SSMB Jack Bulkhead Connector Solder Attachment Turret Terminal, .126 inch D Hole, Rear Mount PE4338](http://www.pasternack.com/ssmb-jack-standard-turret-terminal-connector-pe4338-p.aspx)

URL: <http://www.pasternack.com/ssmb-jack-standard-turret-terminal-connector-pe4338-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

PE4338 CAD Drawing

SSMB Jack Bulkhead Connector Solder Attachment Turret
Terminal, .126 inch D Hole, Rear Mount



DWG TITLE

PE4338

- NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].
4. FITS MIL-C-17 AND EQUIVALENT CABLES.

REV. -

FSCM NO. 53919

CAD FILE 050802

SCALE N/A

SIZE A

2233



Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com