


75 Ohm F Male Connector Twist Attachment for RG59B/U, RG62, RG71



PE44318

Configuration

- F Male Connector
- 75 Ohms
- Straight Body Geometry
- Connector Interface Types: RG59B/U, RG62, RG71

Applications

- General Purpose Test
- Custom Cable Assemblies
- CATV

Description

Pasternack's PE44318 type F , F, Standard, Connector is part of our full line of RF components available for same-day shipping.

Our 75 ohm type F male connector PE44318 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Impedance		75		Ohms

Mechanical Specifications

Size

Length	0.79 in [20.07 mm]
Width	0.433 in [11.00 mm]
Height	0 in [0 mm]
Weight	0.015 lbs [6.8 g]

Material Specifications

Description	Material	Plating
Body	Brass	Nickel
Coupling Nut	Brass	Nickel

Environmental Specifications

Temperature

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

75 Ohm F Male Connector Twist Attachment for RG59B/U, RG62, RG71



PE44318

75 Ohm F Male Connector Twist Attachment for RG59B/U, RG62, RG71 from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [75 Ohm F Male Connector Twist Attachment for RG59B/U, RG62, RG71 PE44318](https://www.pasternack.com/f-male-rg59b-u-rg62-rg71-connector-pe44318-p.aspx)

URL: <https://www.pasternack.com/f-male-rg59b-u-rg62-rg71-connector-pe44318-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE44318 CAD Drawing

75 Ohm F Male Connector Twist Attachment for RG59B/U, RG62, RG71



STRIPPING DIMENSIONS

ASSEMBLY PROCEDURES

1. STRIP CABLE AS SHOWN.
2. SCREW CONNECTOR OVER CABLE UNTIL DIELECTRIC IS FLUSH WITH BODY SHOULDER.

DWG TITLE

PE44318

NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES [mm].
 4. FITS MIL-C-17 AND EQUIVALENT CABLES.

FSCM NO. 53919

CAD FILE 121802

SCALE N/A

SIZE A

127



Pasternack Enterprises, Inc.
 P.O. Box 16759 | Irvine | CA | 92623

Phone: (949) 261-1920 | Fax: (949) 261-7451

Website: www.pasternack.com | E-Mail: sales@pasternack.com