

75 Ohm N Female Bulkhead Mount Connector Solder Attachment Solder Cup Terminal, .640 inch DD Hole



PE4505

Configuration

- N Female Connector
- 75 Ohms
- Straight Body Geometry
- Solder Method
- Connector Interface Types: Solder Cup
- Bulkhead

Features

- Gold Plated Copper Contact

Applications

- General Purpose Test
- Rack and Panel Mount Applications

Description

PE4505 Type N female bulkhead terminal connector has an interface type of Type N female solder cup and a 75 Ohm impedance. Pasternack's Type N female bulkhead connector uses solder as an attachment method.

The Pasternack Type N female bulkhead terminal connector has a PTFE dielectric type. The Pasternack Type N terminal connector has a brass body with nickel plating. Our PE4505 Type N connector uses gold contact.

This Pasternack female Type N bulkhead connector will ship the same business day as purchased. Our bulkhead Type N female connector is part of RF, microwave and millimeter wave components in stock for worldwide shipment. For further information on similar products, our expert technical support and trained sales team can get you the ideal RF connector as per your requirements. PE4505 Type N female bulkhead terminal connector has an interface type of Type N female solder cup and a 75 Ohm impedance. Pasternack's Type N female bulkhead connector uses solder as an attachment method.

The Pasternack Type N female bulkhead terminal connector has a PTFE dielectric type. The Pasternack Type N terminal connector has a brass body with nickel plating. Our PE4505 Type N connector uses gold contact.

This Pasternack female Type N bulkhead connector will ship the same business day as purchased. Our bulkhead Type N female connector is part of RF, microwave and millimeter wave components in stock for worldwide shipment. For further information on similar products, our expert technical support and trained sales team can get you the ideal RF connector as per your requirements.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------|---------|---------|---------|-------|
| Impedance | | 75 | | Ohms |

Mechanical Specifications

Size

| | |
|--------|---------------------|
| Length | 1.428 in [36.27 mm] |
| Width | 0.81 in [20.57 mm] |
| Height | 0.81 in [20.57 mm] |
| Weight | 0.086 lbs [39.01 g] |

75 Ohm N Female Bulkhead Mount Connector Solder Attachment Solder Cup Terminal, .640 inch DD Hole



PE4505

Material Specifications

| Description | Material | Plating |
|-------------|----------|---------|
| Contact | Copper | Gold |
| Insulation | PTFE | |
| Body | Brass | Nickel |

Environmental Specifications

Temperature

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

75 Ohm N Female Bulkhead Mount Connector Solder Attachment Solder Cup Terminal, .640 inch DD Hole from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [75 Ohm N Female Bulkhead Mount Connector Solder Attachment Solder Cup Terminal, .640 inch DD Hole PE4505](#)

URL: <https://www.pasternack.com/n-female-standard-solder-cup-terminal-connector-pe4505-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE4505 CAD Drawing

75 Ohm N Female Bulkhead Mount Connector Solder Attachment Solder Cup Terminal, .640 inch DD Hole

