



SMC Jack Bulkhead Mount Connector  
Solder Attachment Thru Hole PCB

TECHNICAL DATA SHEET

PE45147

**Configuration**

Connector	SMC Jack
Connector Specification	MIL-C-39012
Connector Interface Type	Thru Hole
Attachment Method (Shield/Contact)	Solder
Body Style	Straight
Mount Method	Bulkhead

**Electrical Specifications**

Impedance	50 Ohms
-----------	---------

**Mechanical Specifications**

**Temperature**

Operating Range	-65 to +165 deg C
-----------------	-------------------

**Size**

Length	0.66 in [16.76 mm]
Width/Dia.	0.276 in [7.01 mm]
Height	0.276 in [7.01 mm]
Weight	0.005 lbs [2.27 g]

**Connector**

Type	SMC Jack
Contact Material and Plating	Gold
Contact Plating Specification	MIL-G-45204
Body Material and Plating	Brass, Gold
Body Plating Specification	MIL-G-45204
Dielectric Type	Teflon

**Compliance Certifications** (visit [www.Pasternack.com](http://www.Pasternack.com) for current document)

RoHS Compliant	
REACH Compliant	06/18/2012

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMC Jack Bulkhead Mount Connector Solder Attachment Thru Hole PCB PE45147](#)



## SMC Jack Bulkhead Mount Connector Solder Attachment Thru Hole PCB

### TECHNICAL DATA SHEET

PE45147

#### Plotted and Other Data

Notes:

- Values at +25 °C, sea level

SMC Jack Bulkhead Mount Connector Solder Attachment Thru Hole PCB from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMC Jack Bulkhead Mount Connector Solder Attachment Thru Hole PCB PE45147](http://www.pasternack.com/smc-jack-thru-hole-pcb-connector-pe45147)

URL: <http://www.pasternack.com/smc-jack-thru-hole-pcb-connector-pe45147-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE45147 CAD Drawing

SMC Jack Bulkhead Mount Connector Solder Attachment Thru Hole PCB



DWG TITLE

**PE45147**

- NOTES:  
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
 3. DIMENSIONS ARE IN INCHES [mm].  
 4. FITS MIL-C-17 AND EQUIVALENT CABLES.

FSCM NO. 53919

CAD FILE 020915

SCALE N/A

SIZE A

2233

**PE PASTERNAK**  
 THE ENGINEER'S RF SOURCE  
 Pasternack Enterprises, Inc.  
 P.O. Box 16759 | Irvine | CA | 92623

Phone: (949) 261-1920 | Fax: (949) 261-7451  
 Website: www.pasternack.com | E-Mail: sales@pasternack.com