

### SMA Female to SMB Plug Adapter



## **RF Adapters Technical Data Sheet**

PE9142

### Configuration

- SMA Female Connector 1
- SMB Plug Connector 2

### **Features**

- Max VSWR of 1.3:1 up to 4 GHz
- SMA interface compliant with MIL-STD-348A
- SMB interface compliant with MIL-STD-348A

- 50 Ohm
- Straight Body Geometry
- 30 µ-in minimum contact plating
- Gold Plated Beryllium Copper Contact

### **Applications**

Allows Connection Between Series

General Purpose Test

#### **Description**

Pasternack's PE9142 SMA female to SMB plug adapter is part of our full line of RF components available for same-day shipping. The SMA connector mates mechanically with commercially available 3.5mm and 2.92mm (K) connectors. Our SMA to SMB adapter has a female to plug gender configuration. PE9142 SMA female to SMB plug adapter operates to 4 GHz. The Pasternack RF adapter provides good VSWR of 1.3:1 maximum.

RF adapters are often used to enable connections between two connector types that would otherwise not mate. Certain adapter configurations can also be used to protect connectors on expensive equipment where the number of connect/disconnect cycles is high. An RF, microwave or millimeter wave adapter is connected to the equipment, and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Pasternack also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

#### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		4	GHz
VSWR			1.3:1	
Operating Voltage (AC)			335	Vrms

#### **Mechanical Specifications**

Size

 Length
 0.642 in [16.31 mm]

 Width
 0.25 in [6.35 mm]

 Weight
 0.011 lbs [4.99 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Female to SMB Plug Adapter PE9142

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



## SMA Female to SMB Plug Adapter



## **RF Adapters Technical Data Sheet**

**PE9142** 

Connector 1	Connector 2
SMA Female	SMB Plug
Standard	Standard
MIL-STD-348A	MIL-STD-348A
	SMA Female Standard

#### **Material Specifications**

	Connector 1		Connector 2		
Description	Material	Plating	Material	Plating	
Туре	SMA Female		SMB Plug		
Contact	Beryllium Copper	Gold	Beryllium Copper	Gold	
		30 μ-in minimum		30 μ-in minimum	
Insulation	PTFE		PTFE		
Outer Conductor	Brass	Nickel			
		100 μ-in minimum			
Body			Brass	Nickel	
				100 μ-in minimum	
Coupling Nut			Brass	Nickel	
				100 μ-in minimum	

**Environmental Specifications** 

**Temperature** 

**Operating Range** 

-65 to +165 deg C

Compliance Certifications (see product page for current document)

**Plotted and Other Data** 

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Female to SMB Plug Adapter PE9142

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451



### SMA Female to SMB Plug Adapter



## **RF Adapters Technical Data Sheet**

**PE9142** 

SMA Female to SMB Plug Adapter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Female to SMB Plug Adapter PE9142

URL: https://www.pasternack.com/sma-female-smb-plug-straight-adapter-pe9142-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

# PE9142 CAD Drawing

SMA Female to SMB Plug Adapter

