

20 dB Fixed Attenuator, N Male To N Female Directional Aluminum
 Heatsink Black Anodized Body Rated To 500 Watts Up To 1 GHz

TECHNICAL DATA SHEET

PE7032-20

20 dB Fixed Attenuator, N Male To N Female Directional Aluminum Heatsink Black Anodized Body Rated To 500 Watts Up To 1 GHz

Configuration

Design	Fixed, Directional Attenuator
Connector 1	N Male
Connector 2	N Female
Body Material and Plating	Aluminum Heatsink, Black Anodized

Electrical Specifications

Frequency Range, MHz	DC to 1,000
Impedance, Ohms	50
Attenuation Value, dB	20
Maximum Input Power, Watts	500
Maximum VSWR	1.15:1

Mechanical Specifications

Size

Length, in [mm]	14 [355.6]
Width, in [mm]	6.25 [158.75]
Height, in [mm]	6.25 [158.75]

Connector 1

Type	N Male
------	--------

Connector 2

Type	N Female
------	----------

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [20 dB Fixed Attenuator, N Male To N Female Directional Aluminum Heatsink Black Anodized Body Rated To 500 Watts Up To 1 GHz PE7032-20](#)

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

20 dB Fixed Attenuator, N Male To N Female Directional Aluminum
Heatsink Black Anodized Body Rated To 500 Watts Up To 1 GHz

TECHNICAL DATA SHEET

PE7032-20

Compliance Certifications (visit www.Pasternack.com for current document)

Plotted and Other Data

Notes:

Values at 25 °C, sea level

20 dB Fixed Attenuator, N Male To N Female Directional Aluminum Heatsink Black Anodized Body Rated To 500 Watts Up To 1 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [20 dB Fixed Attenuator, N Male To N Female Directional Aluminum Heatsink Black Anodized Body Rated To 500 Watts Up To 1 GHz PE7032-20](http://www.pasternack.com/20db-fixed-n-female-n-male-500-watts-attenuator-pe7032-20-p.aspx)

URL: <http://www.pasternack.com/20db-fixed-n-female-n-male-500-watts-attenuator-pe7032-20-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

PE7032-20 CAD Drawing

20 dB Fixed Attenuator, N Male To N Female Directional Aluminum Heatsink Black Anodized Body Rated To 500 Watts Up To 1 GHz

P/N	ATTEN.	FIGURE
PE7032-1	1 dB	1
PE7032-2	2 dB	1
PE7032-3	3 dB	1
PE7032-6	6 dB	1
PE7032-10	10 dB	1
PE7032-20	20 dB	1
PE7032-30	30 dB	1




FIGURE 1

NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE

PE7032

FSCM NO. 53919

CAD FILE 022813

SCALE N/A

SIZE A

2231



PASTERNAK®
 Pasternack Enterprises, Inc.
 P.O. Box 16759 | Irvine | CA | 92623
 Phone: (949) 261-1920 | Fax: (949) 261-7451
 Website: www.pasternack.com | E-Mail: sales@pasternack.com