



10 dB Fixed Attenuator, TNC Male to TNC Female Brass  
Nickel Body Rated to 2 Watts Up to 12.4 GHz

RF Fixed Attenuators Technical Data Sheet

PE7051-10

**Features**

- Bidirectional
- DC to 12.4 GHz Frequency Range
- Attenuation 10±0.5 dB
- Max Power 2 Watts (CW)
- VSWR < 1.25:1

**Applications**

- Instrumentation//Precision measurements//Prototyping and characterization//Production systems

**Description**

Pasternack carries a wide range of fixed attenuators with a broad selection of attenuation levels, frequency ranges, and power dissipation ranges. RF microwave attenuators (also known as RF pads) lower the amplitude of a signal (attenuate) a known amount and can be used in a wide variety of applications. These attenuator pads are used when a signal needs to be reduced to protect measurement equipment or other circuitry, to extend the range of power meters and amplifiers, and to impedance match circuits by reducing the VSWR seen by adjacent components. RF attenuators can prevent signal overload in amplifiers, receivers and detectors, adjusting the signal level to a range that is optimal.

Few RF components are as commonly used as fixed coaxial attenuators, and Pasternack carries one of the largest in-stock varieties and ships them same day. The 10 dB Fixed Attenuator PE7051-10 is rated to 2 Watts and operates from DC to 12.4 GHz. The versatile coaxial package uses TNC male to TNC female connectors and is also REACH and RoHS compliant.

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		12.4	GHz
Impedance		50		Ohms
Nominal Attenuation		10		dB
Attenuation Accuracy		0.5		dB
VSWR			1.25:1	
Input Power, CW derated linearly from 2W @ 25°C to 0.5W @ 125°C			2	Watts
Input Power, Peak 5µs pulse, 0.05% duty cycle			250	Watts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [10 dB Fixed Attenuator, TNC Male to TNC Female Brass Nickel Body Rated to 2 Watts Up to 12.4 GHz PE7051-10](#)



10 dB Fixed Attenuator, TNC Male to TNC Female Brass  
Nickel Body Rated to 2 Watts Up to 12.4 GHz

## RF Fixed Attenuators Technical Data Sheet

PE7051-10

### Mechanical Specifications

#### Size

Length	1.36 in [34.54 mm]
Width/Diameter	0.59 in [14.99 mm]
Weight	0.0522 lbs [23.68 g]
Body Material and Plating	Brass, Nickel

#### Configuration

Design	Fixed, Bidirectional
Package Style	Connectorized Module

#### Connectors

Description	Connector 1	Connector 2
Type	TNC Male	TNC Female
Connector Specification	MIL-STD-348	MIL-STD-348
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Coupling Nut Material and Plating	Brass, Nickel	
Body Material and Plating	Brass, Nickel	Brass, Nickel

### Environmental Specifications

#### Temperature

Operating Range	-65 to +125 deg C
-----------------	-------------------

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

10 dB Fixed Attenuator, TNC Male to TNC Female Brass Nickel Body Rated to 2 Watts Up to 12.4 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [10 dB Fixed Attenuator, TNC Male to TNC Female Brass Nickel Body Rated to 2 Watts Up to 12.4 GHz PE7051-10](#)

URL: <https://www.pasternack.com/10db-fixed-tnc-male-tnc-female-2-watts-attenuator-pe7051-10-p.aspx>

# PE7051-10 CAD Drawing

10 dB Fixed Attenuator, TNC Male to TNC Female Brass  
Nickel Body Rated to 2 Watts Up to 12.4 GHz

P/N	ATTEN.	FIGURE
PE7051-1	1 dB	1
PE7051-2	2 dB	1
PE7051-3	3 dB	1
PE7051-6	6 dB	1
PE7051-10	10 dB	1
PE7051-20	20 dB	1
PE7051-30	30 dB	1
PE7051-40	40 dB	1




FIGURE 1  
TNC FEMALE

TNC MALE

STANDARD TOLERANCES
.X ±0.2
.XX ±0.01
.XXX ±0.005

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

NOTES:  
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE  
**PE7051**

FSCM NO. 53919

CAD FILE 022916

SCALE N/A

SIZE A

3045

**PEI PASTERNAK**  
THE ENGINEER'S RF SOURCE

Pasternack Enterprises, Inc.  
P.O. Box 16759 | Irvine | CA | 92623

Phone: (949) 261-1920 | Fax: (949) 261-7451  
Website: www.pasternack.com | E-Mail: sales@pasternack.com