



20 dB Fixed Attenuator, 7/16 DIN Male To SMA Female  
Directional Rated To 50 Watts Up To 7.5 GHz

TECHNICAL DATA SHEET

PE7332-20

**20 dB Fixed Attenuator, 7/16 DIN Male To SMA Female Directional Rated To 50 Watts Up To 7.5 GHz**

**Configuration**

Design	Fixed, Directional Attenuator
Connector 1	7/16 DIN Male
Connector 2	SMA Female
Body Material and Plating	Aluminum Heatsink, Black Anodized

**Electrical Specifications**

Frequency Range, GHz	DC to 7.5
Impedance, Ohms	50
Attenuation Value, dB	20
Maximum Input Power, Watts	50
Maximum VSWR	1.45:1

**Frequency 1**

Range, GHz	DC to 6
VSWR	1.3:1
Attenuation Accuracy, dB	0.75

**Frequency 2**

Range, GHz	6 to 7.5
VSWR	1.45:1
Attenuation Accuracy, dB	0.75

**Mechanical Specifications**

**Temperature**

Operating Range, deg C	-55 to +125
------------------------	-------------

**Size**

Length, in [mm]	4.01 [101.85]
Width, in [mm]	3 [76.2]
Height, in [mm]	3 [76.2]
Weight, lbs [g]	1.796 [814.65]

**Connector 1**

Type	7/16 DIN Male
Contact Material and Plating	Brass, Silver
Hex Size, In.	11/16
Body Material and Plating	Brass, Silver

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [20 dB Fixed Attenuator, 7/16 DIN Male To SMA Female Directional Rated To 50 Watts Up To 7.5 GHz PE7332-20](#)

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.



20 dB Fixed Attenuator, 7/16 DIN Male To SMA Female  
Directional Rated To 50 Watts Up To 7.5 GHz

## TECHNICAL DATA SHEET

PE7332-20

### Connector 2

Type	SMA Female
Contact Material and Plating	Beryllium Copper, Gold
Outer Conductor Material and Plating	Stainless Steel, Passivated
Hex Size, In.	11/16
Body Material and Plating	Stainless Steel, Passivated

### Compliance Certifications (visit [www.Pasternack.com](http://www.Pasternack.com) for current document)

RoHS Compliant	Yes
----------------	-----

### Plotted and Other Data

Notes:	Values at 25 °C, sea level OUTPUT PORT HANDLES 5 WATTS MAX POWER
--------	---

URL: <http://www.pasternack.com/20db-fixed-7-16-male-sma-female-50-watts-attenuator-pe7332-20-p.aspx>

20 dB Fixed Attenuator, 7/16 DIN Male To SMA Female Directional Rated To 50 Watts Up To 7.5 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.


# PE7332-20 CAD Drawing

20 dB Fixed Attenuator, 7/16 DIN Male To SMA Female

Directional Rated To 50 Watts Up To 7.5 GHz

xx	Input Connector	Output Connector
10	7/16 Female	7/16 Male
11	N Female	7/16 Male
12	7/16 Male	7/16 Female
13	7/16 Female	7/16 Female
14	N Male	7/16 Female
15	N Female	7/16 Female
16	7/16 Female	N Male
17	N Female	N Male
18	SMA Female	N Male
19	TNC Female	N Male
20	7/16 Male	N Female
21	7/16 Female	N Female
22	N Male	N Female
23	N Female	N Female
24	SMA Male	N Female
25	SMA Female	N Female
26	TNC Male	N Female
27	TNC Female	N Female
28	7/16 Female	SMA Male
29	N Female	SMA Male
30	SMA Female	SMA Male
31	TNC Female	SMA Male
32	7/16 Male	SMA Female
33	7/16 Female	SMA Female
34	N Male	SMA Female
35	N Female	SMA Female
36	SMA Male	SMA Female
37	SMA Female	SMA Female
38	TNC Male	SMA Female
39	TNC Female	SMA Female
40	7/16 Female	TNC Male
41	N Female	TNC Male
42	SMA Female	TNC Male
43	TNC Female	TNC Male
44	7/16 Male	TNC Female
45	7/16 Female	TNC Female
46	N Male	TNC Female
47	N Female	TNC Female
48	SMA Male	TNC Female
49	SMA Female	TNC Female
50	TNC Male	TNC Female
51	TNC Female	TNC Female

Connector Type	DIM "A" (REF.)
SMA Male	0.68
SMA Female	0.54
TNC Male	0.98
TNC Female	0.94
N Female	0.95
N Male	0.98
7/16 Male	1.12
7/16 Female	1.16



NOTES:  
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
 3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE  
**PE73xx-yy**

FSCM NO. 53919

CAD FILE 102512

SCALE N/A

SIZE A

2233

**PE PASTERNAK®**  
 Pasternack Enterprises, Inc.  
 P.O. Box 16759 | Irvine | CA | 92623  
 Phone: (949) 261-1920 | Fax: (949) 261-7451  
 Website: www.pasternack.com | E-Mail: sales@pasternack.com