



2.5 dB NF, 13 dBm P1dB, 2 GHz to 20 GHz, Low Noise Broadband Amplifier, 14.5 dB Gain, SMA

TECHNICAL DATA SHEET

PE15A3270

The PE15A3270 low noise amplifier operates across a wide frequency range from 2 GHz to 20 GHz. The design utilizes GaAs PHEMT MMIC technology for high efficiency and high linearity. Typical performance includes 14.5 dB small signal gain, 2.5 dB noise figure, up to +13 dBm of output power at P1dB and +23 dBm output IP3, while using a +9V to +15V single DC supply. The design exhibits a very flat gain response across a wide frequency band. Input/output ports are matched for 50 ohms and are DC blocked. The design also incorporates integrated bias sequencing circuitry and voltage regulators to allow for flexible biasing positive voltage supply. The drop-in package is hermetically sealed with field replaceable SMA connectors and has an operating temperature range of -55°C to +85°C. And for added confidence, this rugged package assembly is designed to meet MIL-STD-883 test conditions for Hermeticity and Temperature Cycle.

Features

- LNA Module
- Extremely wide frequency band
- GaAs PHEMT MMIC Technology
- Flat Gain 14.5 dB +/- 0.5 dB
- High Output IP3 +23 dBm
- Output P1dB up to +13 dBm typical
- Regulated Supply and Bias Sequencing
- Hermetically Sealed Module
- Mil Spec Compliant
- Field Replaceable SMA Connectors
- -55°C to +85°C Operating Temperature

Applications

- Electronic Warfare
- Electronic Countermeasures
- Microwave Radio
- VSAT
- Radar
- Fiber Optic
- Space Systems
- Test Instrumentation
- Telecom Infrastructure

Electrical Specifications (TA= 25°C, VDC1 = 12 Vdc)

Description	Minimum	Typical	Maximum	Units
Frequency Range	2		20	GHz
Gain		14.5		dB
Output at 1 dB Compression Point		+13		dBm
Noise Figure		2.5		dB
Operating DC Voltage 1		12		Volts
Operating Temperature Range (OTR)	-55		+85	°C

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.5 dB NF, 13 dBm P1dB, 2 GHz to 20 GHz, Low Noise Broadband Amplifier, 14.5 dB Gain, SMA PE15A3270](#)



2.5 dB NF, 13 dBm P1dB, 2 GHz to 20 GHz, Low Noise Broadband Amplifier, 14.5 dB Gain, SMA

TECHNICAL DATA SHEET

PE15A3270

Performance by Frequency

Description	Min.	Typ.	Max.	Min.	Typ.	Max.	Min.	Typ.	Max.	Units
Frequency Range	2.0 - 6.0			6.0 - 16.0			16.0 - 20.0			GHz
Gain	13	15		12	14.5		11	13		dB
Gain Flatness	±0.25			±0.5			±0.5			dB
Gain Variation Over Temperature	0.015 0.025			0.015 0.025			0.015 0.025			dB/ °C
Noise Figure	3.5 4.5			2.5 3.5			4 5			dB
Input Return Loss	15			20			10			dB
Output Return Loss	13			15			8			dB
Output Power For 1 dB Compression (P1dB)	11	14		10	13		8.5	11.5		dBm
Saturated Output Power (Psat)	17			15.5			14			dBm
Output Third Order Intercept (IP3)	25			23			21			dBm
Supply Current	78			78			78			mA

Mechanical Specifications

Size

Length 0.64 in [16.26 mm]
 Width 0.59 in [14.99 mm]
 Height 0.29 in [7.37 mm]
 Weight 0.055 lbs [24.95 g]

Connector Option Field Replaceable
 Input Connector SMA Female
 Output Connector SMA Female

Environmental Specifications

Temperature

Operating Range -55 to +85 deg C
 Storage Range -65 to +150 deg C

Temperature Cycling MIL-STD-883, Method 101C, Cond B
 Hermetic Seal Gross Leak MIL-STD-883 Method 1014C1/Fine Leak MIL-STD-883, Method 1014A2, 5 x 10-8 atm cc
 ESD Sensitivity ESD Sensitive Material, Transport material in Approved ESD bags. Handle only in ESD Workstation.



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.5 dB NF, 13 dBm P1dB, 2 GHz to 20 GHz, Low Noise Broadband Amplifier, 14.5 dB Gain, SMA PE15A3270](#)



2.5 dB NF, 13 dBm P1dB, 2 GHz to 20 GHz, Low Noise Broadband Amplifier, 14.5 dB Gain, SMA

TECHNICAL DATA SHEET

PE15A3270

Compliance Certifications (visit www.Pasternack.com for current document)


RoHS Compliant

Plotted and Other Data

Notes:

- Values at +25 °C, sea level

Functional Block Diagram



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.5 dB NF, 13 dBm P1dB, 2 GHz to 20 GHz, Low Noise Broadband Amplifier, 14.5 dB Gain, SMA PE15A3270](#)





2.5 dB NF, 13 dBm P1dB, 2 GHz to 20 GHz, Low Noise Broadband Amplifier, 14.5 dB Gain, SMA

TECHNICAL DATA SHEET

PE15A3270

Typical Performance Data





Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.5 dB NF, 13 dBm P1dB, 2 GHz to 20 GHz, Low Noise Broadband Amplifier, 14.5 dB Gain, SMA PE15A3270](#)



2.5 dB NF, 13 dBm P1dB, 2 GHz to 20 GHz, Low Noise Broadband Amplifier, 14.5 dB Gain, SMA

TECHNICAL DATA SHEET

PE15A3270





Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.5 dB NF, 13 dBm P1dB, 2 GHz to 20 GHz, Low Noise Broadband Amplifier, 14.5 dB Gain, SMA PE15A3270](#)



2.5 dB NF, 13 dBm P1dB, 2 GHz to 20 GHz, Low Noise Broadband Amplifier, 14.5 dB Gain, SMA

TECHNICAL DATA SHEET PE15A3270





Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.5 dB NF, 13 dBm P1dB, 2 GHz to 20 GHz, Low Noise Broadband Amplifier, 14.5 dB Gain, SMA PE15A3270](#)



2.5 dB NF, 13 dBm P1dB, 2 GHz to 20 GHz, Low Noise Broadband Amplifier, 14.5 dB Gain, SMA

TECHNICAL DATA SHEET

PE15A3270



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.5 dB NF, 13 dBm P1dB, 2 GHz to 20 GHz, Low Noise Broadband Amplifier, 14.5 dB Gain, SMA PE15A3270](#)



2.5 dB NF, 13 dBm P1dB, 2 GHz to 20 GHz, Low Noise Broadband Amplifier, 14.5 dB Gain, SMA

TECHNICAL DATA SHEET

PE15A3270

2.5 dB NF, 13 dBm P1dB, 2 GHz to 20 GHz, Low Noise Broadband Amplifier, 14.5 dB Gain, SMA from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.5 dB NF, 13 dBm P1dB, 2 GHz to 20 GHz, Low Noise Broadband Amplifier, 14.5 dB Gain, SMA PE15A3270](https://www.pasternack.com/2.5-db-20-ghz-low-noise-broadband-amplifier-14.5-db-gain-sma-pe15a3270-p.aspx)

URL: <https://www.pasternack.com/2.5-db-20-ghz-low-noise-broadband-amplifier-14.5-db-gain-sma-pe15a3270-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE15A3270 CAD Drawing

2.5 dB NF, 13 dBm P1dB, 2 GHz to 20 GHz, Low Noise
Broadband Amplifier, 14.5 dB Gain, SMA



NOTE:
HEAT SINK REQUIRED FOR PROPER OPERATION,
UNIT IS COOLED BY CONDUCTING TO HEAT SINK.

<p>NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].</p>	<p>DWG TITLE PE15A3270</p>	<p>PE PASTERNAK THE ENGINEER'S RF SOURCE Pasternack Enterprises, Inc. P.O. Box 16759 Irvine CA 92623 Phone: (949) 261-1920 Fax: (949) 261-7451 Website: www.pasternack.com E-Mail: sales@pasternack.com</p>
<p>CAD FILE 051716</p>	<p>SCALE N/A</p>	<p>FSCM NO. 53919</p>
<p>SIZE A</p>	<p>2233</p>	<p>9</p>