



## 2 Way SMA Wilkinson Power Divider From 500 MHz to 1,000 MHz Rated at 10 Watts

### Power Dividers Technical Data Sheet

PE2008

#### Features

- 2-Way Power Divider
- Wilkinson Design
- 500 to 1,000 MHz Frequency Range
- Max Power 10 Watts (CW)
- Insertion Loss < 0.2 dB
- Isolation > 22 dB

#### Applications

- Test and Measurement
- Military Communications
- Commercial Communications
- Wireless Communications
- SATCOM

#### Description

Pasternack carries a wide selection of power dividers to fit your needs. These components are essential in many systems, allowing the combination of multiple signals or splitting of a single signal into multiple signals with equal magnitude and phase. Pasternack's resistive and Wilkinson power dividers come with excellent performance featuring minimal loss, high isolation and low VSWR. They are available in both narrow and broad bandwidths with a variety of connector types such as 2.92mm, BNC, N and SMA.

The PE2008 is a 2-way Wilkinson power divider that operates from 500 to 1,000 MHz and can handle up to 10 Watts (CW) with 0.2 dB max insertion loss and 22 dB min isolation. The package interface uses SMA female connectors and is REACH and RoHS compliant.

#### Electrical Specifications

Design	Wilkinson
Number of Output Ports	2

Description	Minimum	Typical	Maximum	Units
Frequency Range	500		1,000	MHz
Impedance		50		Ohms
Input VSWR			1.2:1	
Output VSWR			1.2:1	
Insertion Loss			0.2	dB
Isolation	22			dB
Input Power (CW)			10	Watts

Electrical Specification Notes:  
Max input power rated for load VSWR of 1.25:1 or better.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2 Way SMA Wilkinson Power Divider From 500 MHz to 1,000 MHz Rated at 10 Watts PE2008](#)



## 2 Way SMA Wilkinson Power Divider From 500 MHz to 1,000 MHz Rated at 10 Watts

### Power Dividers Technical Data Sheet

PE2008

#### Mechanical Specifications

##### Size

Length	2.5 in [63.5 mm]
Width	1.5 in [38.1 mm]
Height	0.5 in [12.7 mm]
Weight	0.233 lbs [105.69 g]

##### Configuration

Package Type	Connectorized
Input Connector	SMA Female
Output Connectors	SMA Female

#### Compliance Certifications (visit [www.Pasternack.com](http://www.Pasternack.com) for current document)

RoHS Compliant	
REACH Compliant	12/17/2015

#### Plotted and Other Data

Notes:

2 Way SMA Wilkinson Power Divider From 500 MHz to 1,000 MHz Rated at 10 Watts from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2 Way SMA Wilkinson Power Divider From 500 MHz to 1,000 MHz Rated at 10 Watts PE2008](http://www.pasternack.com/2-way-sma-reactive-power-divider-500-mhz-1000-mhz-10-watts-pe2008-p.aspx)

URL: <http://www.pasternack.com/2-way-sma-reactive-power-divider-500-mhz-1000-mhz-10-watts-pe2008-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE2008 CAD Drawing

2 Way SMA Wilkinson Power Divider From 500 MHz to 1,000 MHz Rated at 10 Watts



**STANDARD TOLERANCES**  
 .X ±0.2  
 .XX ±0.1  
 .XXX ±0.05

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

**NOTES:**  
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
 3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE  
**PE2008**

FSCM NO. 53919

CAD FILE 050416

SCALE N/A

SIZE A

3045

**PE PASTERNAK**  
 THE ENGINEER'S RF SOURCE  
 Pasternack Enterprises, Inc.  
 P.O. Box 16759 | Irvine | CA | 92623  
 Phone: (949) 261-1920 | Fax: (949) 261-7451  
 Website: www.pasternack.com | E-Mail: sales@pasternack.com