



50 Ohm 3 Way N Power Divider From 800 MHz
to 2.5 GHz Rated at 50 Watts

TECHNICAL DATA SHEET

PE2072

50 Ohm 3 Way N Power Divider From 800 MHz to 2.5 GHz Rated at 50 Watts

Configuration

Input Connector	N Female
Frequency Range, GHz	0.8 to 2.5
Number of Output Ports	3

Electrical Specifications

Frequency Range, GHz	0.8 to 2.5
Impedance, Ohms	50
Maximum Insertion Loss, dB	0.6
Maximum Input Power, Watts	50
Maximum Input VSWR	1.3:1
Minimum Isolation, dB	20
Phase Balance, Degrees	± 3
Flatness, dB	0.35

Mechanical Specifications

Temperature

Operating Range, deg C	-30 to +70
------------------------	------------

Size

Length, in [mm]	3.69 [93.73]
Width, in [mm]	4.53 [115.06]
Height, in [mm]	0.875 [22.23]

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant	Yes
----------------	-----

Plotted and Other Data

Notes:	Values at 25 °C, sea level
--------	----------------------------

50 Ohm 3 Way N Power Divider From 800 MHz to 2.5 GHz Rated at 50 Watts from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [50 Ohm 3 Way N Power Divider From 800 MHz to 2.5 GHz Rated at 50 Watts PE2072](http://www.pasternack.com/3-way-n-reactive-power-divider-0.8-ghz-2.5-ghz-50-watts-pe2072-p.aspx)

URL: <http://www.pasternack.com/3-way-n-reactive-power-divider-0.8-ghz-2.5-ghz-50-watts-pe2072-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

PE2072 CAD Drawing

50 Ohm 3 Way N Power Divider From 800 MHz to 2.5 GHz Rated at 50 Watts



NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE
PE2072

FSCM NO. 53919

PE PASTERNAK®
 Pasternack Enterprises, Inc.
 P.O. Box 16759 | Irvine | CA | 92623
 Phone: (949) 261-1920 | Fax: (949) 261-7451
 Website: www.pasternack.com | E-Mail: sales@pasternack.com

CAD FILE 072409 SCALE N/A SIZE A 127