



62 dB Gain, 17 dBm P1dB, 0.01 GHz to 3.5 GHz, Broadband AC Low Noise Amplifier, Bench-Top, 110/220VAC, 1.3 dB Noise Figure, SMA

TECHNICAL DATA SHEET

PE15A63023

The PE15A63023 is an AC powered Bench-Top Low Noise Amplifier that operates across a broadband frequency range from 10 MHz to 3.5 GHz. This 50 Ohm highly linear design exhibits impressive typical performance that includes 62 dB gain, 1.3 dB noise figure, +17 dBm P1dB, and +26 dBm output IP3. Maximum RF input power (CW) is -20 dBm. The rugged MIL Grade aluminium package is finished in gray paint and has SMA Female connectors at the RF input and output ports, and an indicator light on the front panel. The rear panel supports an IEC 320-C14 AC power socket (IEC 320-C13 plug required), a fuse compartment, an On/Off switch, and a dedicated package common ground connector. The module supports a wide operating AC voltage range from 110VAC to 220VAC with 60 mA supply current. Designed for high reliability, the package supports an integrated heatsink and cooling fan and is suitable for outdoor operation (moisture exposure dependent on temperature and humidity conditions). The amplifier has an operational temperature range from -40°C to +85°C and meets a series of environmental test conditions including Altitude, Vibration, Humidity, and Shock.

Features

- AC Powered Bench-Top Low Noise Amplifier
- 10 MHz to 3.5 GHz
- High Linearity
- High Small Signal Gain 62 dB typ
- Low Noise Figure 1.3 dB typ
- Output VSWR 1.7:1 typ
- Output P1dB +17 dBm typ
- Output Psat +18 dBm typ
- Output IP3 +26 dBm typ
- AC Supply 110-220VAC @ 60 mA
- Max RF Input Power (CW) -20 dBm
- 50 Ohm Design
- Integrated Heatsink and Cooling Fan
- RF Input and Output SMA Female Connectors
- On/Off Switch and Indicator Light
- Operational Temperature Range -40°C to +85°C
- Rugged MIL Grade Aluminum Package Design with Gray Paint finish
- Guaranteed Environmental Test Conditions Altitude, Vibration, Humidity, Shock

Applications

- Test & Measurement
- 5G Communication
- Wireless Infrastructure
- Military & Commercial Communications
- Military Electronic Systems
- Research & Development
- Microwave Radio
- VSAT
- Fiber Optics

Electrical Specifications (TA= 25°C)

Description	Minimum	Typical	Maximum	Units
Frequency Range	0.01		3.5	GHz
Gain	58	62		dB
Gain Flatness		±1.25		dB
Gain Variation over Temp.		±1		dB/°C
Output at 1 dB Compression Point		+17		dBm
Saturation Output Power		+18		dBm
Output 3 rd Intercept Point		+26		dBm
Reverse Isolation		-75		dB
Noise Figure		1.3	1.5	dB
Input VSWR		2.2:1		
Output VSWR		1.7:1		

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [62 dB Gain, 17 dBm P1dB, 0.01 GHz to 3.5 GHz, Broadband AC Low Noise Amplifier, Bench-Top, 110/220VAC, 1.3 dB Noise Figure, SMA PE15A63023](#)



62 dB Gain, 17 dBm P1dB, 0.01 GHz to 3.5 GHz, Broadband AC Low Noise Amplifier, Bench-Top, 110/220VAC, 1.3 dB Noise Figure, SMA

TECHNICAL DATA SHEET

PE15A63023

Operating AC Voltage	110 to 220	VAC
Supply Current (AC 110-220V)	60	mA
Operating Temperature Range (OTR)	-40	+85 °C

Performance by Frequency

Biassing Up Procedure

Step 1	Connect input and output with 50 Ohm source and load with in band return loss better than 10dB.
Step 2	Connect AC Plug
Step 3	Flip switch to "ON" position

Power OFF Procedure

Step 1	Flip switch to "OFF" position
Step 2	Remove AC Plug
Step 3	Remove RF Connection

Absolute Maximum Rating

Parameter	Rating
Supply Voltage	110V to 220V AC
RF Input Power *	-20dBm

*Note: Maximum RF input power is defined to protect the amplifier from damage. Input power may be increased at the users ownrisk to achieve the full output power of the amplifier. Please reference gain and power curves and monitor the temperature.

Mechanical Specifications

Size	
Length	6.46 in [164.08 mm]
Width	5.83 in [148.08 mm]
Height	2.28 in [57.91 mm]
Weight	2.53 lbs [1.15 kg]
Input Connector	SMA Female
Output Connector	SMA Female

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [62 dB Gain, 17 dBm P1dB, 0.01 GHz to 3.5 GHz, Broadband AC Low Noise Amplifier, Bench-Top, 110/220VAC, 1.3 dB Noise Figure, SMA PE15A63023](#)



62 dB Gain, 17 dBm P1dB, 0.01 GHz to
3.5 GHz, Broadband AC Low Noise Amplifier, Bench-
Top, 110/220VAC, 1.3 dB Noise Figure, SMA

TECHNICAL DATA SHEET

PE15A63023

Environmental Specifications

Temperature

Operating Range

-40 to +85 deg C

Storage Range

-50 to +105 deg C

Humidity

100% RH at 35°C, 95%RH at 40°C

Shock

20G for 11msec half sine wave, 3 axis both directions

Vibration

25g RMS (15 degrees 2KHz) endurance, 1 hour per axis

Altitude

30,000 ft.

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [62 dB Gain, 17 dBm P1dB, 0.01 GHz to 3.5 GHz, Broadband AC Low Noise Amplifier, Bench-Top, 110/220VAC, 1.3 dB Noise Figure, SMA PE15A63023](#)




62 dB Gain, 17 dBm P1dB, 0.01 GHz to 3.5 GHz, Broadband AC Low Noise Amplifier, Bench-Top, 110/220VAC, 1.3 dB Noise Figure, SMA


TECHNICAL DATA SHEET **PE15A63023**

Typical Performance Data


Gain




Input VSWR



Output VSWR



Isolation



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [62 dB Gain, 17 dBm P1dB, 0.01 GHz to 3.5 GHz, Broadband AC Low Noise Amplifier, Bench-Top, 110/220VAC, 1.3 dB Noise Figure, SMA PE15A63023](#)




62 dB Gain, 17 dBm P1dB, 0.01 GHz to 3.5 GHz, Broadband AC Low Noise Amplifier, Bench-Top, 110/220VAC, 1.3 dB Noise Figure, SMA


TECHNICAL DATA SHEET

PE15A63023


Gain vs. Output Power




P1dB vs. Frequency



OIP3 vs. Frequency



Saturated Power vs. Frequency



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [62 dB Gain, 17 dBm P1dB, 0.01 GHz to 3.5 GHz, Broadband AC Low Noise Amplifier, Bench-Top, 110/220VAC, 1.3 dB Noise Figure, SMA PE15A63023](#)




62 dB Gain, 17 dBm P1dB, 0.01 GHz to 3.5 GHz, Broadband AC Low Noise Amplifier, Bench-Top, 110/220VAC, 1.3 dB Noise Figure, SMA


TECHNICAL DATA SHEET

PE15A63023


Noise Figure(0.01-0.1GHz)



Noise Figure(0.1-3.5GHz)



Pout vs. Pin



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [62 dB Gain, 17 dBm P1dB, 0.01 GHz to 3.5 GHz, Broadband AC Low Noise Amplifier, Bench-Top, 110/220VAC, 1.3 dB Noise Figure, SMA PE15A63023](#)



62 dB Gain, 17 dBm P1dB, 0.01 GHz to
3.5 GHz, Broadband AC Low Noise Amplifier, Bench-
Top, 110/220VAC, 1.3 dB Noise Figure, SMA

TECHNICAL DATA SHEET

PE15A63023

62 dB Gain, 17 dBm P1dB, 0.01 GHz to 3.5 GHz, Broadband AC Low Noise Amplifier, Bench-Top, 110/220VAC, 1.3 dB Noise Figure, SMA from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [62 dB Gain, 17 dBm P1dB, 0.01 GHz to 3.5 GHz, Broadband AC Low Noise Amplifier, Bench-Top, 110/220VAC, 1.3 dB Noise Figure, SMA PE15A63023](https://www.pasternack.com/60-db-gain-29-dbm-ip3-1.1-db-3.5-ghz-low-noise-broadband-amplifier-sma-pe15a63023-p.aspx)

URL: <https://www.pasternack.com/60-db-gain-29-dbm-ip3-1.1-db-3.5-ghz-low-noise-broadband-amplifier-sma-pe15a63023-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE15A63023 CAD Drawing

62 dB Gain, 17 dBm P1dB, 0.01 GHz to 3.5 GHz, Broadband AC Low Noise Amplifier, Bench-Top, 110/220VAC, 1.3 dB Noise Figure, SMA



ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	B	ECO-12844	06/12/2023	DZINN	TGALLA

PASTERNAK an INFINIT@ brand		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 SCALE: NONE SHEET: 1 OF 1
Website: www.Pasternack.com Phone: 1.866.727.8376 1.949.261.1920		DESCRIPTION: 62 dB GAIN, 16 dBm P1dB, 0.01 - 3.5 GHz, BROADBAND AC LOW NOISE GaAs AMPLIFIER, BENCH-TOP, 115/220VAC, 1.3 dB NOISE FIGURE, SMA
SIZE: A	CAGE CODE: 53919 DRAWN BY: DZINN ITEM NO.: PE15A63023	

UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE INCHES, DIMENSIONS IN [] ARE MILLIMETERS.

TOLERANCES:

.X = ±.2 [5]	FRACTIONS ± 1/32
.XX = ±.02 [0.5]	ANGLES ± 1°
.XXX = ±.005 [0.13]	

CABLE LENGTH TOLERANCES:

≤12 [305]	±.1 [25] / -0
>12 [305] ≤ 60 [1524]	±.2 [51] / -0
>60 [1524] ≤ 120 [3048]	±.4 [102] / -0
>120 [3048] ≤ 300 [7620]	±.6 [152] / -0
>300 [7620]	±.9 [229] / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE. UN-DIMENSIONED NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION.

NOTES:

- LABEL PER ILS-100-02. FOR INTERNAL REFERENCE ONLY. LABEL LOCATION FOR REFERENCE ONLY

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.