



SMA Female to N Male Precision Cable
Using 160 Series Coax, RoHS

TECHNICAL DATA SHEET

PE306

SMA Female to N Male Precision Cable Using 160 Series Coax, RoHS

Configuration

Connector 1	SMA Female
Connector 2	N Male
Cable Type	160 Series

Electrical Specifications

Frequency Range, GHz	DC to 18
Impedance, Ohms	50
Maximum VSWR	1.4:1
Velocity of Propagation, %	69.5
RF Shielding, dB	90
Maximum Operating Voltage, Vrms	1,200

Typical Performance by Frequency

Frequency 1

Frequency, GHz	2
VSWR	1.07:1
Insertion Loss	0.2 dB/ft [0.66 dB/m]

Frequency 2

Frequency, GHz	6
VSWR	1.15:1
Insertion Loss	0.38 dB/ft [1.25 dB/m]

Frequency 3

Frequency, GHz	10
VSWR	1.21:1
Insertion Loss	0.55 dB/ft [1.8 dB/m]

Frequency 4

Frequency, GHz	14
VSWR	1.27:1
Insertion Loss	0.7 dB/ft [2.3 dB/m]

Frequency 5

Frequency, GHz	16
VSWR	1.28:1
Insertion Loss	0.8 dB/ft [2.62 dB/m]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Female to N Male Precision Cable Using 160 Series Coax, RoHS PE306](#)

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.



SMA Female to N Male Precision Cable Using 160 Series Coax, RoHS

TECHNICAL DATA SHEET

PE306

Frequency 6

Frequency, GHz	18
VSWR	1.26:1
Insertion Loss	0.88 dB/ft [2.89 dB/m]

Electrical Specification Notes:

Short lengths up to 24" long may exhibit VSWR measurements up to 9% higher.

Mechanical Specifications

Cable Assembly

Cable Type 160 Series

Temperature

Temperature Operating Range, deg C	-48 to +204
Diameter, in [mm]	0.17 [4.32]
Weight, lbs [g]	0.038 [17.24]
Cable Color	Blue
One Time Minimum Bend Radius, in [mm]	1 [25.4]

Cable

Center Conductor Type	Solid
Cable Inner Conductor	Copper Clad Steel, Silver
No of Shields	3
Dielectric Type	PTFE
Jacket Material	FEP
Jacket Diameter, in [mm]	0.163 [4.14]

Connector 1

Type	SMA Female
Configuration	Straight
Inner Conductor Material and Plating	Gold
Body Material and Plating	Passivated Stainless Steel
Dielectric Type	PTFE

Connector 2

Type	N Male
Configuration	Straight
Inner Conductor Material and Plating	Gold
Coupling Nut Material and Plating	Passivated Stainless Steel
Hex Size, in.	13/16
Torque, in-lbs [Nm]	15 [1.7]
Body Material and Plating	Passivated Stainless Steel
Dielectric Type	PTFE

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Female to N Male Precision Cable Using 160 Series Coax, RoHS PE306](#)

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.



SMA Female to N Male Precision Cable
Using 160 Series Coax, RoHS

TECHNICAL DATA SHEET

PE306

Compliance Certifications (visit www.Pasternack.com for current document)
RoHS Compliant Yes

Plotted and Other Data
Notes:

Values at 25 °C, sea level

SMA Female to N Male Precision Cable Using 160 Series Coax, RoHS from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Female to N Male Precision Cable Using 160 Series Coax, RoHS PE306](#)

URL: <http://www.pasternack.com/sma-female-n-male-300-series-cable-assembly-pe306-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

PE306 CAD Drawing

SMA Female to N Male Precision Cable Using 160 Series Coax, RoHS



How To Order		Part # Ext.	Length In Inches	Part # Ext.	Length In Centimeters
Part Number Configuration PE3 [zzz] [yy] - [xx] [uu] 00 - 99999 LF = Lead Free < Blank > = Standard Note: LF applies only to RF cables		-12	12"	-25CM	25Cm
Examples PE3000LF-100 PE3000-100 PE3000LF-100CM PE3000-100CM		-24	24"	-50CM	50Cm
CM = Centimeters < Blank > = Inches Length		-36	36"	-75CM	75Cm
		-48	48"	-100CM	100Cm
		-60	60"	-125CM	125Cm
		-xx	Custom Length	-xxCM	Custom Length

NOTES:
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
 3. DIMENSIONS ARE IN INCHES [mm].
 4. LENGTH TOLERANCE IS ± 1.5% OR 3/8", WHICHEVER IS GREATER.

DWG TITLE
PE306

PE PASTERNAK®
 Pasternack Enterprises, Inc.
 P.O. Box 16759 | Irvine | CA | 92623
 Phone: (949) 261-1920 | Fax: (949) 261-7451
 Website: www.pasternack.com | E-Mail: sales@pasternack.com

REV. A	FSCM NO. 53919	CAD FILE 071012	SCALE N/A	SIZE A	2233
--------	----------------	-----------------	-----------	--------	------