



2.92mm Male to 2.92mm Male Cable Using PE-P102 Coax, RoHS

TECHNICAL DATA SHEET

PE371

Configuration

Connector 1 2.92mm Male Connector 2 2.92mm Male Cable Type PE-P102

Electrical Specifications

DC to 40 GHz Frequency Range Impedance 50 Ohms Maximum VSWR 1.4:1 Velocity of Propagation 76 % 90 dB RF Shielding Peak Power 550 Watts

Typical Performance by Frequency

Frequency 1

Frequency 6 GHz **VSWR** 1.25:1 0.75 dB/ft [2.46 dB/m] Insertion Loss

Power Handling, Watts 160

Frequency 2

12 GHz Frequency **VSWR** 1.25:1 Insertion Loss 1.08 dB/ft [3.54 dB/m]

Power Handling 110 Watts

Frequency 3

Frequency 18 GHz **VSWR** 1.25:1 1.36 dB/ft [4.46 dB/m] Insertion Loss

Power Handling 89 Watts

Frequency 4

Frequency 26.5 GHz **VSWR** 1.4:1

1.67 dB/ft [5.48 dB/m] Insertion Loss

73 Watts **Power Handling**

Frequency 5

Frequency 40 GHz **VSWR** 1.4:1

Insertion Loss 2.13 dB/ft [6.99 dB/m]

Power Handling 58 Watts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 2.92mm Male to 2.92mm Male Cable Using PE-P102 Coax, RoHS PE371

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





2.92mm Male to 2.92mm Male Cable Using PE-P102 Coax, RoHS

TECHNICAL DATA SHEET

PE371

Mechanical Specifications

Temperature

Temperature Operating Range -65 to +165 deg C

Size

Diameter 0.38 in [9.65 mm]

Cable Color Gray

One Time Minimum Bend Radius 0.32 in [8.13 mm]

Cable

Cable TypePE-P102Inner Conductor TypeStrandedCable Inner ConductorCopper, Silver

No of Shields 3
Dielectric Type PTFE
Jacket Material ETFE

Jacket Diameter 0.102 in [2.59 mm]

Connector 1

Type 2.92mm Male Configuration Straight

Inner Conductor Material and Plating

Inner Conductor Plating Specification

Coupling Nut Material and Plating

Beryllium Copper, Gold

ASTM-B488 50µ In. Minimum

Passivated Stainless Steel

Coupling Nut Plating Specification SAE-AMS-2700 Hex Size 5/16 Inch

Torque 5/16 Inch
8 in-lbs [0.9 Nm]

Body Material and Plating Passivated Stainless Steel Body Plating Specification SAE-AMS-2700

Dielectric Type PPO

Connector 2

Type 2.92mm Male Configuration Straight

Inner Conductor Material and Plating

Inner Conductor Plating Specification

Coupling Nut Material and Plating

Beryllium Copper, Gold

ASTM-B488 50µ In. Minimum

Passivated Stainless Steel

Coupling Nut Plating Specification SAE-AMS-2700
Hex Size 5/16 Inch
Torque 8 in-lbs [0.9 Nm]

Body Material and Plating Passivated Stainless Steel

Body Plating Specification SAE-AMS-2700

Dielectric Type PPO

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant Yes

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 2.92mm Male to 2.92mm Male Cable Using PE-P102 Coax, RoHS PE371

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





2.92mm Male to 2.92mm Male Cable Using PE-P102 Coax, RoHS

TECHNICAL DATA SHEET

PE371

Plotted and Other Data

Notes:

• Values at +25 °C, sea level

2.92mm Male to 2.92mm Male Cable Using PE-P102 Coax, RoHS from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 2.92mm Male to 2.92mm Male Cable Using PE-P102 Coax, RoHS PE371

URL: http://www.pasternack.com/2.92mm-male-2.92mm-male-pe-p102-cable-assembly-pe371-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone**: (866) 727-8376 or (949) 261-1920 • **Fax**: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

