



RF Cable Assemblies Technical Data Sheet

PE3740


Configuration

Connector 1: SMA Male Right AngleConnector 2: SMC Plug Right Angle

Cable Type: RG316

Features

- Max Frequency 3 GHz
- FEP Jacket



Applications

· General Purpose

· Laboratory Use

Description

Pasternack's PE3740 SMA male right angle to SMC plug right angle cable using RG316 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to SMC cable assembly has a male to plug gender configuration with 50 ohm flexible RG316 coax. The PE3740 SMA male to SMC plug cable assembly operates to 3 GHz. The right angle SMA and right angle SMC interfaces on the RG316 cable allow for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description Frequency Range		Minimum	Typical	Maximum	Units GHz
		DC		3	
VSWR				1.5:1	
Capacitance			32 [104.99]		pF/ft [pF/m]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male Right Angle to SMC Plug Right Angle Cable Using RG316 Coax PE3740

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451





RF Cable Assemblies Technical Data Sheet

PE3740

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	3	GHz
Insertion Loss (Max.)	0.16	0.23	0.37	0.53	0.58	dB/ft
	0.52	0.75	1.21	1.74	1.9	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the conectors. Insertion Loss is estimated as 0.4dB of connector loss.

Mechanical Specifications

Cable Assembly

 Diameter
 0.451 in [11.46 mm]

 Weight
 0.031 lbs [14.06 g]

Cable

Cable TypeRG316Impedance50 OhmsInner Conductor TypeStranded

Inner Conductor Material and Plating Copper Clad Steel, Silver

Dielectric Type PTFE
Number of Shields 1

Shield Layer 1 Silver Plated Copper Braid

Jacket Material FEP, Tan

Jacket Diameter 0.098 in [2.49 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male Right Angle to SMC Plug Right Angle Cable Using RG316 Coax PE3740

© 2018 Pasternack Enterprises All Rights Reserved





RF Cable Assemblies Technical Data Sheet

PE3740

Connectors

Description	Connector 1	Connector 2 SMC Plug Right Angle	
Туре	SMA Male Right Angle		
Specification	MIL-STD-348A	MIL-STD-348A	
Impedance	50 Ohms	50 Ohms	
Contact Material and Plating	Brass, Gold	Beryllium Copper, Gold	
Contact Plating Specification	50μ in. minimum	30μ in. minimum	
Dielectric Type	Teflon	Teflon	
Body Material and Plating	Brass, Nickel	Brass, Nickel	
Body Plating Specification	100μ in. minimum	100μ in. minimum	
Coupling Nut Material and Plating		Brass, Nickel	
Coupling Nut Plating Specification		100μ in. minimum	
Hex Size	5/16 in	1/4 in.	
Torque	5 in-lbs [0.57 Nm]	3 in-lbs [0.34 Nm]	

Mechanical Specification Notes:

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

• Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male Right Angle to SMC Plug Right Angle Cable Using RG316 Coax PE3740

^{*}All cable assemblies have a length tolerance of 1.5% or ± 3/8", whichever is greater.






RF Cable Assemblies Technical Data Sheet

PE3740

Typical Performance Data



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male Right Angle to SMC Plug Right Angle Cable Using RG316 Coax PE3740






RF Cable Assemblies Technical Data Sheet

PE3740

How to Order



Example: PE3740-12 = 12 inches long cable

PE3740-100cm = 100 cm long cable

SMA Male Right Angle to SMC Plug Right Angle Cable Using RG316 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male Right Angle to SMC Plug Right Angle Cable Using RG316 Coax PE3740

URL: https://www.pasternack.com/sma-male-smc-plug-rg316u-cable-assembly-pe3740-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623

Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

PE3740 CAD Drawing
SMA Male Right Angle to SMC Plug Right Angle Cable Using RG316 Coax

