



RF Cable Assemblies Technical Data Sheet

PE3M0004

Configuration

• Connector 1: M39012/16-0014(BNC Male)

Connector 2: M39012/03-0503(N Female Bulkhead)

• Cable: M17/60-RG142

Features

- Max Frequency 4 GHz
- 69.5% Phase Velocity
- · Double Shielded
- FEP Jacket
- · Lot Traceability
- · J-STD-Soldering
- · Qualified (QPL) cable and connectors
- RF Test Plots
- Test Report
- · In stock and ready to ship

Applications

Hi-Rel

Avionics

• MIL-DTL-17 Requirements

SATCOM

ECM

Description

Pasternack's MIL-DTL-17 cable assemblies are part of our full line of reliable RF components available for same-day shipping. These commercial-off-the-shelf (COTS), military grade cable assemblies are designed and processed with high reliability in mind. MIL-PRF-39012 connectors and MIL-C-17 coaxial cable are assembled using J-STD soldering processes and WHMA-A-620 workmanship criteria. The combination of materials, processing and acceptance testing work together to create a dependable cable assembly for applications where performance over time is important or the cost of failure is high. Each finished MIL-DTL-17 cable assembly is traceable to its component lots and a test report is available for every lot produced.

Our MIL-DTL-17 cable assembly datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave cable assemblies allow designers to configure and customize their signal connections however they like. Whether the need is to provide reliable mil-spec connections or fielding dependable RF cable assemblies, Pasternack has the right cable assemblies for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same day.

Referenced Specifications

IPC/WHMA-A-620 Requirements and Acceptance for Cable and Wire Harness Assemblies MIL-DTL-17 Cables, Radio Frequency, Flexible and Semirigid, General Specification for

Radio Frequency Connector Interfaces for MIL-DTL-3643, MIL-DTL-3650, MIL-DTL-3655, MIL-MIL-STD-348

DTL-25516, MIL-PRF-31031, MIL-PRF-39012, MIL-PRF-49142, MIL-PRF...

MIL-PRF-39012 Connectors, Coaxial, Radio Frequency, General Specification for IPC J-STD-001 Requirements for Soldered Electrical and Electronic Assemblies

IPC J-STD-006 Requirements for Electronic Grade Solder Alloys and Fluxed and Non-Fluxed Solid Solders for

Electronic Soldering Applications Marking of Electrical Insulating Materials

SAE AS5942 **SAE AS23053** Insulation Sleeving, Electrical, Heat Shrinkable, General Specifications For

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: MIL-DTL-17 BNC Male to N Female Bulkhead Cable Using M17/60-RG142 Coax PE3M0004

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





RF Cable Assemblies Technical Data Sheet

PE3M0004

SAE AS22520

Crimping Tools, Wire Termination, General Specification For

Material Specifications

Specification
M17/60-RG142 in accordance with MIL-DTL-17
M39012/16-0014 in accordance with MIL-PRF-39012
M39012/03-0503 in accordance with MIL-PRF-39012
M23053/5-106-0 in accordance with SAE AS23053
M23053/5-106-0 in accordance with SAE AS23053
SN63 in accordance with J-STD-006

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		4	GHz
VSWR			1.6:1	
Velocity of Propagation		69.5		%
Capacitance		29.3 [96.13]		pF/ft [pF/m]
Dielectric Withstanding Voltage (AC)			1,500	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.4	1	3	4	GHz
Insertion Loss (Max.)	0.044	0.093	0.153	0.293	0.35	dB/ft
	0.14	0.31	0.5	0.96	1.15	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1dB per connector.

Mechanical Specifications

Cable Assembly

Description	Minimum	Typical	Maximum	Units
Cable Outer Diameter	0.19	0.195	0.2	in
Weight			0.21 [95.25]	lbs [g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: MIL-DTL-17 BNC Male to N Female Bulkhead Cable Using M17/60-RG142 Coax PE3M0004

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





RF Cable Assemblies Technical Data Sheet

PE3M0004

*Length Tolerances: +0.5, -0 inches for Length ≤ 1 foot; +1, -0 inches for Length >1 to 5 feet; +2, -0 inches for Length >5 to 10 feet; +3, -0 inches for Length >10 to 25 feet and +2%, -0 inches for Length >25 feet.

Cable Characteristics

Description	Specification	
Cable Type	M17/60-RG142	
Impedance	50 Ohms	
Inner Conductor Type	Solid	
Inner Conductor Material and Plating	Copper Clad Steel, Silver	
Dielectric Type	PTFE	
Number of Shields	2	
Shield Layer 1	Silver Clad Copper	
Shield Layer 2	Silver Clad Copper	
Outer Conductor Diameter	0.171 in [4.34 mm]	A W
Jacket Material	FEP	

Connector Characteristics

Description	Connector 1	Connector 2
Туре	BNC Male	N Female Bulkhead
Specification	MIL-PRF-39012	MIL-PRF-39012
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Phosphor Bronze, Gold
Contact Plating Specification	MIL-G-45204	MIL-G-45204
Dielectric Type	Teflon	Teflon
Outer Conductor Material and Plating		Brass, Silver
Outer Conductor Plating Specification		QQ-S-365
Body Material and Plating	Brass, Silver	Brass, Silver
Body Plating Specification	QQ-S-365	QQ-S-365
Coupling Nut Material and Plating		Brass, Silver
Coupling Nut Plating Specification		QQ-S-365
Seal Gasket Material	Silicone Rubber	Silicone Rubber
Contact Gage Specification	0.210 to 0.230 in	0.187 to 0.207 in
Insulator Gage Specification	0.208 to 0.228 in	

Mechanical Specification Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: MIL-DTL-17 BNC Male to N Female Bulkhead Cable Using M17/60-RG142 Coax PE3M0004

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451





RF Cable Assemblies Technical Data Sheet

PE3M0004

Environmental Specifications

Description	Specification
Temperature Operating Range	-55 to +165 deg C

Compliance Certifications (see product page for current document)

Process Specifications

Process	Specification
Soldering	in accordance with J-STD-001, class 3
Crimping	dies in accordance with SAE AS22520
Marking	shall meet the adherence requirements of SAE AS5942
Workmanship	shall be in accordance with IPC/WHMA-A-620, class 3

Tests and Inspections

or annu morphorateme	
Description	Sampling
Connector Gaging (pin and insulator position)	100%
Insertion Loss	100%
VSWR	100%
Dielectric Withstanding Voltage (DWV)	100%
Visual - workmanship, configuration and marking	100%
Length	C=0, 1.5 AQL
Mass	C=0, 1.5 AQL

Plotted and Other Data

Notes:

Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: MIL-DTL-17 BNC Male to N Female Bulkhead Cable Using M17/60-RG142 Coax PE3M0004






RF Cable Assemblies Technical Data Sheet

PE3M0004

How to Order



Example: PE3M0004-12 = 12 inches long cable PE3M0004-100cm = 100 cm long cable

MIL-DTL-17 BNC Male to N Female Bulkhead Cable Using M17/60-RG142 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: MIL-DTL-17 BNC Male to N Female Bulkhead Cable Using M17/60-RG142 Coax PE3M0004

URL: https://www.pasternack.com/bnc-male-n-female-m17-60-rg142-cable-assembly-pe3m0004-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

PE3M0004 CAD DrawingMIL-DTL-17 BNC Male to N Female Bulkhead Cable Using M17/60-RG142 Coax

