



### RF Cable Assemblies Technical Data Sheet


PE3W06405

## Configuration

- Connector 1: N Female BulkheadConnector 2: SMA Male Right Angle
- Cable Type: PE-P195

#### **Features**

- Max Frequency 4 GHz
- 70% Phase Velocity
- · Triple Shielded
- FEP Jacket



# **Applications**

· General Purpose

· Laboratory Use

#### **Description**

Pasternack's PE3W06405 type N female bulkhead to SMA male right angle cable using PE-P195 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to SMA cable assembly has a female to male gender configuration with 50 ohm flexible PE-P195 coax. The PE3W06405 type N female to SMA male cable assembly operates to 4 GHz. The right angle SMA interface on the PE-P195 cable allows for easier connections in tight spaces. Our RF cable assembly with type N bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The triple shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		4	GHz
VSWR			1.5:1	
Velocity of Propagation		70		%
Capacitance		29 [95.14]		pF/ft [pF/m]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Female Bulkhead to SMA Male Right Angle Cable Using PE-P195 Coax PE3W06405

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





### RF Cable Assemblies Technical Data Sheet

PE3W06405

#### **Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	4	GHz
Insertion Loss (Max.)	0.05	0.08	0.12	0.19	0.26	dB/ft
	0.16	0.26	0.39	0.62	0.85	dB/m

**Electrical Specification Notes:** 

Insertion Loss does not include the loss of connectors. Insertion Loss is estimated as 0.3dB of connector loss.

#### **Mechanical Specifications**

#### **Cable Assembly**

Cable

Cable Type Impedance

Inner Conductor Type

Inner Conductor Material and Plating

Dielectric Type Number of Shields Shield Layer 1 Shield Layer 2 Shield Layer 3

Jacket Material

Jacket Diameter

Repeated Minimum Bend Radius

PE-P195 50 Ohms

Solid

Copper Clad Steel, Silver

PTFE 3

Silver Plated Copper Braid

Aluminum Tape

Silver Plated Copper Braid

FEP, Tan

0.195 in [4.95 mm]

1 in [25.4 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Female Bulkhead to SMA Male Right Angle Cable Using PE-P195 Coax PE3W06405





# RF Cable Assemblies Technical Data Sheet

PE3W06405

#### **Connectors**

Description	Connector 1	Connector 2	
Туре	N Female Bulkhead	SMA Male Right Angle	
Specification		MIL-STD-348A	
Impedance	50 Ohms	50 Ohms	
Contact Material and Plating		Brass, Gold	
Contact Plating Specification		50 μin minimum	
Dielectric Type		PTFE	
Body Material and Plating	Brass, Nickel	Brass, Nickel	
Body Plating Specification		100 μin minimum	
Coupling Nut Material and Plating		Brass, Nickel	
Coupling Nut Plating Specification		100 μin minimum	
Hex Size		5/16 inch	
Torque		3 in-lbs [0.34 Nm]	

Mechanical Specification Notes:

Compliance Certifications (see product page for current document)

**Plotted and Other Data** 

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Female Bulkhead to SMA Male Right Angle Cable Using PE-P195 Coax PE3W06405

<sup>\*</sup>All cable assemblies have a length tolerance of 1.5% or ± 3/8", whichever is greater.





### RF Cable Assemblies Technical Data Sheet

PE3W06405

#### **How to Order**



Example: PE3W06405-12 = 12 inches long cable

PE3W06405-100cm = 100 cm long cable

N Female Bulkhead to SMA Male Right Angle Cable Using PE-P195 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Female Bulkhead to SMA Male Right Angle Cable Using PE-P195 Coax PE3W06405

URL: https://www.pasternack.com/n-female-sma-male-pe-p195-cable-assembly-pe3w06405-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

**PE3W06405 CAD Drawing**N Female Bulkhead to SMA Male Right Angle Cable Using PE-P195 Coax

