



# **RF Cable Assemblies Technical Data Sheet**


# PE3W01018/HS

# Configuration

- Connector 1: N Female BulkheadConnector 2: SMB Plug Right Angle
- Cable Type: PE-C100-LSZH

### **Features**

- Max Frequency 4 GHz
- Shielding Effectivity > 90 dB
- 66% Phase Velocity
- · Double Shielded
- LSZH Jacket



# **Applications**

· General Purpose

· Laboratory Use

### Description

Pasternack's PE3W01018/HS type N female bulkhead to SMB plug right angle cable using PE-C100-LSZH coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to SMB cable assembly has a female to plug gender configuration with 50 ohm flexible PE-C100-LSZH coax. The PE3W01018/HS type N female to SMB plug cable assembly operates to 4 GHz. The right angle SMB interface on the PE-C100-LSZH cable allows for easier connections in tight spaces. Our RF cable assembly with type N bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Female Bulkhead to SMB Plug Right Angle Cable Using PE-C100-LSZH Coax with Heat-Shrink PE3W01018/HS





# RF Cable Assemblies Technical Data Sheet

# PE3W01018/HS

### **Electrical Specifications**

| Description             | Minimum | Typical       | Maximum | Units        |
|-------------------------|---------|---------------|---------|--------------|
| Frequency Range         | DC      |               | 4       | GHz          |
| VSWR                    |         | 735           | 1.5:1   |              |
| Velocity of Propagation |         | 66            |         | %            |
| RF Shielding            | 90      |               |         | dB           |
| Capacitance             |         | 30.8 [101.05] |         | pF/ft [pF/m] |
| Inductance              |         | 0.077 [0.25]  |         | uH/ft [uH/m] |
| Operating Voltage (AC)  |         |               | 250     | Vrms         |
| Jacket Spark            |         |               | 2,000   | Vrms         |

### Specifications by Frequency

| Description           | F1   | F2   | F3   | F4   | F5   | Units |
|-----------------------|------|------|------|------|------|-------|
| Frequency             | 0.1  | 0.25 | 0.5  | 1    | 4    | GHz   |
| Insertion Loss (Max.) | 0.07 | 0.12 | 0.17 | 0.24 | 0.52 | dB/ft |
|                       | 0.23 | 0.39 | 0.56 | 0.79 | 1.71 | dB/m  |

**Electrical Specification Notes:** 

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.3dB connector loss.

# **Mechanical Specifications**

# **Cable Assembly**

Diameter 0.81 in [20.57 mm]
Weight 0.088 lbs [39.92 g]

#### Cable

Cable TypePE-C100-LSZHImpedance50 OhmsInner Conductor TypeSolid

Inner Conductor Material and Plating Copper Clad Steel Dielectric Type PE

Dielectric Type P
Number of Shields 2

Shield Layer 1Aluminum TapeShield Layer 2Tinned Copper BraidJacket MaterialLSZH, BlackJacket Diameter0.109 in [2.77 mm]

One Time Minimum Bend Radius 0.25 in [6.35 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Female Bulkhead to SMB Plug Right Angle Cable Using PE-C100-LSZH Coax with Heat-Shrink PE3W01018/HS

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





# **RF Cable Assemblies Technical Data Sheet**

# PE3W01018/HS

Repeated Minimum Bend Radius Bending Moment Flat Plate Crush Tensile Strength 1 in [25.4 mm] 0.1 lbs-ft [0.14 N-m] 10 lbs/in [0.18 Kg/mm] 15 lbs [6.8 Kg]

#### Connectors

| Description                           | Connector 1       | Connector 2 SMB Plug Right Angle |  |
|---------------------------------------|-------------------|----------------------------------|--|
| Туре                                  | N Female Bulkhead |                                  |  |
| Specification                         | MIL-STD-348A      | MIL-STD-348A                     |  |
| Impedance                             | 50 Ohms           | 50 Ohms                          |  |
| Mating Cycles                         | 100               |                                  |  |
| Contact Material and Plating          | Brass, Gold       | Beryllium Copper, Gold           |  |
| Contact Plating Specification         | 30μ in. minimum   | 30μ in. minimum                  |  |
| Dielectric Type                       | Teflon            | Teflon                           |  |
| Outer Conductor Material and Plating  | Brass, Nickel     |                                  |  |
| Outer Conductor Plating Specification | 100μ in. minimum  |                                  |  |
| Body Material and Plating             | Brass, Nickel     | Brass, Nickel                    |  |
| Body Plating Specification            | 100μ in. minimum  | 100μ in. minimum                 |  |

Mechanical Specification Notes:

# **Environmental Specifications**

**Temperature** 

Operating Range -40 to +85 deg C

Compliance Certifications (see product page for current document)

# **Plotted and Other Data**

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Female Bulkhead to SMB Plug Right Angle Cable Using PE-C100-LSZH Coax with Heat-Shrink PE3W01018/HS

<sup>\*</sup>All cable assemblies have a length tolerance of 1.5% or ± 3/8", whichever is greater.








# **RF Cable Assemblies Technical Data Sheet**

# PE3W01018/HS

### **Typical Performance Data**



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Female Bulkhead to SMB Plug Right Angle Cable Using PE-C100-LSZH Coax with Heat-Shrink PE3W01018/HS





# **RF Cable Assemblies Technical Data Sheet**

### PE3W01018/HS

#### **How to Order**



Example: PE3W01018/HS-12 = 12 inches long cable PE3W01018/HS-100cm = 100 cm long cable

N Female Bulkhead to SMB Plug Right Angle Cable Using PE-C100-LSZH Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Female Bulkhead to SMB Plug Right Angle Cable Using PE-C100-LSZH Coax with HeatShrink PE3W01018/HS

URL: https://www.pasternack.com/n-female-smb-plug-pe-c100-lszh-cable-assembly-pe3w01018-hs-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

**PE3W01018/HS CAD Drawing** N Female Bulkhead to SMB Plug Right Angle Cable Using PE-C100-LSZH Coax with HeatShrink

