



RF Cable Assemblies Technical Data Sheet

PE3W01114LF/HS

Configuration


· Connector 1: MCX Jack

Connector 2: SMA Male Right Angle

• Cable Type: RG316-DS

Features

- Max Frequency 3 GHz
- 70% Phase Velocity
- · Double Shielded
- FEP Jacket



Applications

· General Purpose

· Laboratory Use

Description

Pasternack's PE3W01114LF/HS MCX jack to SMA male right angle cable using RG316-DS coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack MCX to SMA cable assembly has a jack to male gender configuration with 50 ohm flexible RG316-DS coax. The PE3W01114LF/HS MCX jack to SMA male cable assembly operates to 3 GHz. The right angle SMA interface on the RG316-DS cable allows for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.6:1	
Velocity of Propagation		70		%
Capacitance		29.4 [96.46]		pF/ft [pF/m]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: MCX Jack to SMA Male Right Angle Cable Using RG316-DS Coax with HeatShrink, LF Solder PE3W01114LF/HS

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





RF Cable Assemblies Technical Data Sheet

PE3W01114LF/HS

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Max.)	0.08 0.26	0.12 0.39	0.18 0.59	0.26 0.85	0.47 1.54	dB/ft dB/m

Electrical Specification Notes:

The Insertion Loss does not include the loss of the connectors. The Insertion Loss is estimated as 0.3dB connector loss.

Mechanical Specifications

Cable Assembly

Cable

Cable Type Impedance

Inner Conductor Type

Inner Conductor Material and Plating

Dielectric Type Number of Shields Shield Layer 1

Shield Layer 2 Jacket Material

Jacket Diameter

Repeated Minimum Bend Radius

RG316-DS 50 Ohms Stranded

Copper Clad Steel, Silver

PTFE

Silver Plated Copper Braid Silver Plated Copper Braid

FEP, Tan

0.114 in [2.9 mm]

0.6 in [15.24 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: MCX Jack to SMA Male Right Angle Cable Using RG316-DS Coax with HeatShrink, LF Solder PE3W01114LF/HS

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





RF Cable Assemblies Technical Data Sheet

PE3W01114LF/HS

Connectors

Description	Connector 1	Connector 2 SMA Male Right Angle	
Туре	MCX Jack		
Specification		MIL-STD-348A	
Impedance	50 Ohms	50 Ohms	
Contact Material and Plating		Brass, Gold	
Contact Plating Specification		50 μin minimum	
Dielectric Type		PTFE	
Body Material and Plating	Brass, Nickel	Brass, Nickel	
Body Plating Specification		100 μin minimum	
Coupling Nut Material and Plating		Brass, Nickel	
Coupling Nut Plating Specification		100 μin minimum	
Hex Size		5/16 inch	
Torque		3 in-lbs [0.34 Nm]	

Mechanical Specification Notes:

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: MCX Jack to SMA Male Right Angle Cable Using RG316-DS Coax with HeatShrink, LF Solder PE3W01114LF/HS

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

^{*}All cable assemblies have a length tolerance of 1.5% or ± 3/8", whichever is greater.






RF Cable Assemblies Technical Data Sheet

PE3W01114LF/HS

Typical Performance Data



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: MCX Jack to SMA Male Right Angle Cable Using RG316-DS Coax with HeatShrink, LF Solder PE3W01114LF/HS

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451





RF Cable Assemblies Technical Data Sheet

PE3W01114LF/HS

How to Order



Example: PE3W01114LF/HS-12 = 12 inches long cable PE3W01114LF/HS-100cm = 100 cm long cable

MCX Jack to SMA Male Right Angle Cable Using RG316-DS Coax with HeatShrink, LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: MCX Jack to SMA Male Right Angle Cable Using RG316-DS Coax with HeatShrink, LF Solder PE3W01114LF/HS

URL: https://www.pasternack.com/mcx-jack-sma-male-rg316-ds-cable-assembly-pe3w01114lf-hs-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W01114LF/HS CAD Drawing
MCX Jack to SMA Male Right Angle Cable Using RG316-DS Coax with HeatShrink, LF Solder

