

Product Features

- Mini WiFi Rubber Duck Antenna
- 2400-2500 MHz Freq Range
- 5.0dBi Omni Radiation Pattern

Description

The PE51078 swivel style Mini Rubber Duck Antenna provides excellent performance in multiple wireless applications. Its small size and rugged construction is perfect for both indoor and portable wireless systems.

Specifications ⁽¹⁾

Parameter	Value	Units	Description
Minimum Frequency	2400	MHz	
Maximum Frequency	2500	MHz	
Impedance	50	Ohms	
Gain	5.5	dBi	
Polarization	O	Omni	
RF Power Rating	30	W	Max
Maximum VSWR	<2.0	ratio	Between Min and Max Freq
Length	198	mm	7.8 inches
Connector Type		RP-SMA(m)	Swivel Style SMA
Operating Temperature	-40 - +60	Deg C	



Ordering Information

Part Number	Description
PE51078	2400-2500 MHz 5dBi Rubber Duck, Reverse Polarity –SMA Male

(1) Pasternack reserves the right to change specifications or information without notice.

(2) All Specifications "Typical" values