

Product Features

- WIMAX Freq Range
- 3300-3800 MHz
- 30 W Power Handling
- High Gain, 2dBi Omni Radiation Pattern
- Right Angle SMA Style

Specifications ⁽¹⁾

Parameter	Value	Units	Description
Minimum Frequency	3300	MHz	
Maximum Frequency	3800	MHz	
Impedance	50	Ohms	
Gain	2	dBi	Max Gain
Polarization	Vertical		
Max Input Pwr	30	W	Watts (Max)
Maximum VSWR	<2.0	ratio	
Length	108	mm	4.25 inches
Weight	12	g	.42 oz
Connector Type		SMA(M)	Right Angle SMA male
Operating Temperature	-40 to +60	Deg C	



Ordering Information

Part Number	Description
PE51084	3300-3800 MHz Rubber Duck Antenna With SMA Male Right Angle Connector

(1) Pasternack reserves the right to change specifications or information without notice.

(2) All Specifications "Typical" values