

RF Connectors Technical Data Sheet



PE45881

Configuration

- 4.3-10 Plug Connector
- 50 Ohms
- Straight Body Geometry

Features

- Max. Operating Frequency 6 GHz
- Excellent VSWR of 1.03:1

Applications

- General Purpose Test
- Custom Cable Assemblies
- Medical
- Military and Aerospace
- Quantum Computing

Connector Interface Types: 0.141 Cable

Non-Magnetic Design

Silver Plated Brass Contact

Magnetic Susceptibility 10⁻⁵

Description

Pasternack's PE45881, 4.3-10, Non-Magnetic, Connector is part of our full line of RF components available for same-day shipping. Our 4.3-10 plug connector operates up to a maximum frequency of 6 GHz and offers excellent VSWR of 1.03:1. Pasternack's Non Magnetic connectors are manufactured with materials that are especially adapted to non magnetism. Our non-magnetic connectors have a susceptibility of around 10⁻⁵, as opposed to 10⁻² for standard connectors made of brass/nickel materials. As a result, our non-magnetic connectors are transparent to the magnetic field, which means no field distortion and a higher Signal-to-Noise Ratio (SNR).

Our 4.3-10 plug connector PE45881 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same-day.

Electrical Specifications

Minimum	Typical	Maximum	Units
DC		6	GHz
		1.03:1	
		0.05	dB
		335	Vrms
	50		Ohms
		1,000	Vrms
5,000			MOhms
	DC	DC 50	DC 6 1.03:1 0.05 335 50 1,000

Mechanical Specifications

Size	
Length	
Width	

0.43 in [10.90 mm] 0.21 in [5.26 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 4.3-10 Plug Non-Magnetic Connector Crimp/Solder Attachment for 0.141 Cable PE45881

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

© 2020 Pasternack Enterprises All Rights Reserved







PE45881

Height 0.21 in [5.26 mm] Weight 0.00 lbs [0.90 g] Mating Cycles 500 Cycles **Material Specifications** Material Description Plating Brass Silver Contact Copper-Tin-Zinc Alloy Body Brass Gasket **EPDM Rubber Environmental Specifications** Temperature -55 to +90 deg C **Operating Range** Compliance Certifications (see product page for current document) **Plotted and Other Data** Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 4.3-10 Plug Non-Magnetic Connector Crimp/Solder Attachment for 0.141 Cable PE45881


Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com







PE45881



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 4.3-10 Plug Non-Magnetic Connector Crimp/Solder Attachment for 0.141 Cable PE45881

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

© 2020 Pasternack Enterprises All Rights Reserved



RF Connectors Technical Data Sheet



PE45881

4.3-10 Plug Non-Magnetic Connector Crimp/Solder Attachment for 0.141 Cable from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 4.3-10 Plug Non-Magnetic Connector Crimp/Solder Attachment for 0.141 Cable PE45881

URL: https://www.pasternack.com/4.3-10-plug-0.141-cable-connector-pe45881-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com

PE45881 CAD Drawing

4.3-10 Plug Non-Magnetic Connector Crimp/Solder Attachment for 0.141 Cable

