

30 dB With 5 Bit Programmable TTL Controlled Attenuator, 2.92mm Female To 2.92mm Female, 1 dB Steps From 100 MHz To 40 GHz



TECHNICAL DATA SHEET

PE70A5002

The PE70A5002 is a 5 Bit Programmable 30 dB Pin Diode Attenuator with Step Resolution as Low as 1 dB over the Operating Frequency Range from 0.1 GHz to 40 GHz. The RF Input/Output Connectors are 2.92mm Female. Along with a 15 Pin Micro-D Female Control Socket. The unit is shipped with a Micro-D Mating Connector.

Features

- 5 Bit Programmable 30 dB Pin Diode Attenuator
- 0.1 GHz to 40 GHz Frequency Range
- 30 dB Attenuation Range
- Step Resolution of 1 dB

- Insertion Loss 8 dB Typ
- RF Connectors are 2.92mm Female
- 15 Pin Micro-D Female Connector

Applications

- Electronic Warfare
- Military & Space
- Test & Measurement
- Radar

Military Communications Systems

Electrical Specifications (Values at 25°C, sea level)

Description	Minimum	Typical	Maximum	Units
Frequency Range	0.1		40	GHz
Mean Attenuation Range	0		30	dB
Insertion Loss		8		dB
Input VSWR		2.5:1		
Power Rating			+24	dBm
Input at 1 dB Compression Point		+20		dBm
Power Handling Capacity			+24 CW	dBm
Accuracy of Attenuation				
0 dB to 30 dB		±2.5		dB
Step Size	1			dB
Switching Time				
On Time			1	μs
Off Time			0.5	μs
Logic Input				
Logic "0" (Bit Off)	0		0.8	Volts
Logic "1" (Bit On)	2		5	Volts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 30 dB With 5 Bit Programmable TTL Controlled Attenuator, 2.92mm Female To 2.92mm Female, 1 dB Steps From 100 MHz To 40 GHz PE70A5002

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451



30 dB With 5 Bit Programmable TTL Controlled Attenuator, 2.92mm Female To 2.92mm Female, 1 dB Steps From 100 MHz To 40 GHz



TECHNICAL DATA SHEET

PE70A5002

Mechanical Specifications

Size

 Length
 2 in [50.8 mm]

 Width
 1.8 in [45.72 mm]

 Height
 0.5 in [12.7 mm]

 Weight
 0.14 lbs [63.5 g]

 Connector 1
 2.92mm Female

 Connector 2
 2.92mm Female

Environmental Specifications

Temperature

Operating Range -50 to +85 deg C Storage Range -65 to +125 deg C

Humidity MIL-STD-202F, METHOD 103B COND. B Shock MIL-STD-202F, METHOD 213B COND. B Vibration MIL-STD-202F, METHOD 204D COND. B Altitude MIL-STD-202F, METHOD 105C COND. B Temperature Cycling MIL-STD-202F, METHOD 107

Salt Spray

MIL-STD-202F, METHOD 107

MIL-STD-202F, METHOD 105C COND. B

Compliance Certifications (visit www.Pasternack.com for current document)

Not RoHS Compliant

REACH Compliant 12/17/2014

Plotted and Other Data


Notes:

- Values at +25 °C, sea level
- ESD Sensitive Material, Transport material in Approved ESD bags. Handle only in approved ESD Workstation.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 30 dB With 5 Bit Programmable TTL Controlled Attenuator, 2.92mm Female To 2.92mm Female, 1 dB Steps From 100 MHz To 40 GHz PE70A5002

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451










TECHNICAL DATA SHEET

PE70A5002

Performance Data








Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 30 dB With 5 Bit Programmable TTL Controlled Attenuator, 2.92mm Female To 2.92mm Female, 1 dB Steps From 100 MHz To 40 GHz PE70A5002

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451









TECHNICAL DATA SHEET

PE70A5002






-40°C @ -30dB Attenuation




+85°C @ -30dB Attenuation



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 30 dB With 5 Bit Programmable TTL Controlled Attenuator, 2.92mm Female To 2.92mm Female, 1 dB Steps From 100 MHz To 40 GHz PE70A5002

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451








TECHNICAL DATA SHEET

PE70A5002






-40°C Insertion Loss & Return Loss



+85°C Insertion Loss & Return Loss



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 30 dB With 5 Bit Programmable TTL Controlled Attenuator, 2.92mm Female To 2.92mm Female, 1 dB Steps From 100 MHz To 40 GHz PE70A5002

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451



30 dB With 5 Bit Programmable TTL Controlled Attenuator, 2.92mm Female To 2.92mm Female, 1 dB Steps From 100 MHz To 40 GHz



TECHNICAL DATA SHEET

PE70A5002

30 dB With 5 Bit Programmable TTL Controlled Attenuator, 2.92mm Female To 2.92mm Female, 1 dB Steps From 100 MHz To 40 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 30 dB With 5 Bit Programmable TTL Controlled Attenuator, 2.92mm Female To 2.92mm Female, 1 dB Steps From 100 MHz To 40 GHz PE70A5002

URL: https://www.pasternack.com/30db-programmable-2.92mm-female-2.92mm-female-0-watts-attenuator-pe70a5002-p. aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

PE70A5002 CAD Drawing

30 dB With 5 Bit Programmable TTL Controlled Attenuator, 2.92mm Female To 2.92mm Female, 1 dB Steps From 100 MHz To 40 GHz

