



Reflective SPDT Ultra-Wideband PIN Diode Switch Operating from 1 MHz to 75 GHz Up to 15 dBm, 400 nsec and 1.85mm

PIN Diode Switches Technical Data Sheet

PE71S1110

Features

- Ultra-Wideband SPDT PIN Diode Switch
- 1 MHz to 75 GHz
- 50 Ohm Reflective Design
- Integrated TTL Driver
- Insertion Loss: 4.8 dB typ
- Isolation: 35 dB typ
- Switching Speed: 400 nsec typ
- Maximum RF input Power: +15 dBm
- Single Bias Voltage: +5Vdc
- Field Replaceable 1.85mm Female RF Connectors
- Operational Temperature Range -40°C to +85°C
- Rugged and Compact Aluminum Gold Plated Package Design
- Guaranteed Environmental Test Conditions Altitude, Vibration, Humidity, Shock

Applications

- Test & Measurement
- 5G Communication
- Military Electronic Systems
- Wireless Infrastructure
- Fiber Optics
- Research & Development

Description

The PE71S1110 is a single pole double throw (SPDT) PIN diode switch that operates across an ultra-wideband frequency from 1 MHz to 75 GHz. The 50 ohm reflective design supports TTL compatible driver circuitry for accurate logic control. Impressive typical performance includes 4.8 dB insertion loss, 35 dB isolation, and 400 nsec switching speed. The switch requires a +5Vdc bias voltage, and has maximum input power handling of up to +15 dBm. The rugged and compact package supports field replaceable 1.85mm female RF connectors and solder terminal pins for DC bias voltage and TTL control. The switch is designed for high reliability with a wide operational temperature range of -40°C to +85°C, and meets a series of environmental test conditions including Altitude, Vibration, Humidity, and Shock.

Electrical Specifications (@ +25°C)

TTL Control

Off/Isolation: 0 to 0.8 V
On/Low Loss: 2.8 to 5 V

Description	Minimum	Typical	Maximum	Units
Frequency Range	0.001		75	GHz
Impedance		50		Ohms
VSWR		2:1	2.5:1	
Insertion Loss		4.8	7.5	dB
IL Temperature Coefficient		0.003		dB/degC
Isolation	26	35		dB
Switching Time		400	500	ns
0.1dB Compression Point		+15		dBm
Input IP3		45		dBm
RF Input Power (CW)			15	dBm
DC Power Dissipation		0.5		Watt
Positive Operating Voltage		5		Vdc
Current @ 5 Vdc			80	mA

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reflective SPDT Ultra-Wideband PIN Diode Switch Operating from 1 MHz to 75 GHz Up to 15 dBm, 400 nsec and 1.85mm PE71S1110](#)



Reflective SPDT Ultra-Wideband PIN Diode Switch Operating from 1 MHz to 75 GHz Up to 15 dBm, 400 nsec and 1.85mm

PIN Diode Switches Technical Data Sheet

PE71S1110

Operating Temperature -40 +85 deg C

Electrical Specification Notes:

TTL pins cannot be connected to the negative voltage otherwise the internal driver will be damaged.

Absolute Maximum Ratings

Biasing	+5V ± 10%
---------	-----------

Mechanical Specifications

Size

Length	0.94 in [23.88 mm]
Width	0.47 in [11.94 mm]
Height	0.67 in [17.02 mm]
Weight	0.04 lbs [18.14 g]
Design	Reflective, SPDT
RF Input/Output Connector	Field Replaceable 1.85mm Female

Environmental Specifications

Temperature

Operating Range	-40 to +85 deg C
Storage Range	-50 to +105 deg C

Humidity	100% RH at 35°C, 95% RH at 40°C
Shock	20G for 11msec half sinewave, 3 axis both directions
Vibration	25g RMA (15 degrees 2KHz) endurance, 1 hour per axis
Altitude	30,000 ft

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reflective SPDT Ultra-Wideband PIN Diode Switch Operating from 1 MHz to 75 GHz Up to 15 dBm, 400 nsec and 1.85mm PE71S1110](#)




Reflective SPDT Ultra-Wideband PIN Diode Switch Operating from 1 MHz to 75 GHz Up to 15 dBm, 400 nsec and 1.85mm

PIN Diode Switches Technical Data Sheet


PE71S1110

Typical Performance Data


Insertion Loss @+25°C




Input VSWR @+25°C



Output VSWR @+25°C



Isolation @+25°C



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reflective SPDT Ultra-Wideband PIN Diode Switch Operating from 1 MHz to 75 GHz Up to 15 dBm, 400 nsec and 1.85mm PE71S1110](#)




Reflective SPDT Ultra-Wideband PIN Diode Switch Operating from 1 MHz to 75 GHz Up to 15 dBm, 400 nsec and 1.85mm


PIN Diode Switches Technical Data Sheet

PE71S1110


Insertion Loss @-40°C




Input VSWR @-40°C



Output VSWR @-40°C



Isolation @-40°C



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reflective SPDT Ultra-Wideband PIN Diode Switch Operating from 1 MHz to 75 GHz Up to 15 dBm, 400 nsec and 1.85mm PE71S1110](#)




Reflective SPDT Ultra-Wideband PIN Diode Switch Operating from 1 MHz to 75 GHz Up to 15 dBm, 400 nsec and 1.85mm


PIN Diode Switches Technical Data Sheet

PE71S1110


Insertion Loss @+85°C




Input VSWR @+85°C



Output VSWR @+85°C



Isolation @+85°C



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reflective SPDT Ultra-Wideband PIN Diode Switch Operating from 1 MHz to 75 GHz Up to 15 dBm, 400 nsec and 1.85mm PE71S1110](#)




Reflective SPDT Ultra-Wideband PIN Diode Switch Operating from 1 MHz to 75 GHz Up to 15 dBm, 400 nsec and 1.85mm


PIN Diode Switches Technical Data Sheet

PE71S1110

Switching Speed



Switching Speed



Reflective SPDT Ultra-Wideband PIN Diode Switch Operating from 1 MHz to 75 GHz Up to 15 dBm, 400 nsec and 1.85mm from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reflective SPDT Ultra-Wideband PIN Diode Switch Operating from 1 MHz to 75 GHz Up to 15 dBm, 400 nsec and 1.85mm PE71S1110](#)

URL:

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE71S1110 CAD Drawing

Reflective SPDT Ultra-Wideband PIN Diode Switch Operating from 1 MHz to 75 GHz Up to 15 dBm, 400 nsec and 1.85mm



TRUTH TABLE

TTL Control Voltage THRESHOLD	Low(0)=0~0.8V High(1)=2.8~5V
Control Input TTL	Signal Path State
0	J0-J1
1	J0-J2

ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
A		INITIAL RELEASE	03/30/2023	BPUCHASKI	TGALLA

REVISION	1	2	3	4	5	6
----------	---	---	---	---	---	---

PE PASTERNAK
an INFINITIB brand

Website: www.Pasternack.com
Phone: 1.866.727.8376 | 1.949.261.1920

DESCRIPTION
Reflective SPDT Ultra-Wideband PIN Diode Switch Operating from 1 MHz to 75 GHz, Up to 15 dBm, 400 nsec and 1.85mm

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
 .X = ±.2 [5] | FRACTIONS ± 1/32
 .XX = ±.02 [.5] | ANGLES ± 1°
 .XXX = ±.005 [.13]
 CABLE LENGTH TOLERANCES:
 ≤12 [305] = +1 [25] / -0
 >12 [305] ≤ 60 [1524] = +2 [51] / -0
 >60 [1524] ≤ 120 [3048] = +4 [102] / -0
 >120 [3048] ≤ 300 [7620] = +6 [152] / -0
 >300 [7620] = +5% / -0

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

SCALE NONE SHEET 1 OF 1

SIZE A CAGE CODE 53919 DRAWN BY BPUCHASKI ITEM NO. PE71S1110 REV A

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.