



D-Sub Receptacle Right Angle Contact Crimp/  
Solder Attachment For RG58, RG141, RG303

TECHNICAL DATA SHEET

PE4816

**D-Sub Receptacle Right Angle Contact Crimp/Solder Attachment For RG58, RG141, RG303**

**Configuration**

Connector	D-Sub Receptacle
Connector Interface Type	RG58, RG141, RG303
Cable Attachment Method (Shield/Contact)	Crimp/Solder
Body Style	Right Angle

**Electrical Specifications**

Impedance, Ohms	50
-----------------	----

**Mechanical Specifications**

**Size**

Length, in [mm]	0.755 [19.18]
Height, in [mm]	0.715 [18.16]
Weight, lbs [g]	0.006 [2.72]

**Connector**

Type	D-Sub Receptacle
Contact Material and Plating	Gold
Body Material and Plating	Brass, Gold
Dielectric Type	PTFE

**Compliance Certifications** (visit [www.Pasternack.com](http://www.Pasternack.com) for current document)

**Plotted and Other Data**

Notes:	Values at 25 °C, sea level
--------	----------------------------

D-Sub Receptacle Right Angle Contact Crimp/Solder Attachment For RG58, RG141, RG303 from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [D-Sub Receptacle Right Angle Contact Crimp/Solder Attachment For RG58, RG141, RG303 PE4816](http://www.pasternack.com/d-sub-receptacle-right-angle-contact-crimp-solder-attachment-for-rg58-rg141-rg303-connector-pe4816)

URL: <http://www.pasternack.com/d-sub-receptacle-standard-rg58-rg141-rg303-connector-pe4816-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

# PE4816 CAD Drawing

D-Sub Receptacle Right Angle Contact Crimp/Solder Attachment For RG58, RG141, RG303



## STRIPPING DIMENSIONS

## ASSEMBLY PROCEDURES

1. STRIP CABLE AS SHOWN & SLIDE FERRULE OVER CABLE.
2. INSTALL CABLE INTO BODY OF CONNECTOR AND SOFT SOLDER CENTER CONDUCTOR IN PLACE.
3. CRIMP FERRULE & SOLDER CAP IN PLACE.

## CRIMP SIZE REQUIRED

FERRULE: .213" HEX CRIMP TOOL



Pasternack Enterprises, Inc.  
 P.O. Box 16759 | Irvine | CA | 92623  
 Phone: (949) 261-1920 | Fax: (949) 261-7451  
 Website: www.pasternack.com | E-Mail: sales@pasternack.com

DWG TITLE

**PE4816**

FSCM NO. 53919

NOTES:  
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  
 3. DIMENSIONS ARE IN INCHES [mm].  
 4. FITS MIL-C-17 AND EQUIVALENT CABLES.

CAD FILE 061002

SCALE N/A

SIZE A

127