

10 dB Fixed Attenuator, N Male To 7/16 DIN Female Directional Rated To 100 Watts Up To 6 GHz



TECHNICAL DATA SHEET

PE7205-10

10 dB Fixed Attenuator, N Male To 7/16 DIN Female Directional Rated To 100 Watts Up To 6 GHz

Pasternack Enterprises line of 100W Attenuators operate from DC to 6 GHz, and are available in 42 different 7/16 DIN, N, SMA and TNC in-series and between-series connector combinations. Our 100W Attenuators are manufactured with Passivated Stainless Steel SMA, TNC and N connectors, and Silver Plated Brass 7/16 DIN connectors. Pasternack 100W Attenuators come in 3 dB, 6 dB, 10 dB, 20 dB, 30 dB, 40 dB, 60 dB values and will operate from -55 to +125 degrees C. Additional connector combinations are available beyond the 42 standard designs, upon request.

- · 100W average power and 2,000W peak power handling capability
- · Operate to 6 GHz
- Temperature range of -55 to +125 degrees C
- · 42 in-series and between series combinations
- 7/16 DIN, SMA, N, TNC Male and Female connectors are available
- · Other connector combinations available upon request

Configuration

Design Fixed, Directional Attenuator
Connector 1 N Male
Connector 2 7/16 DIN Female
Body Material and Plating Aluminum Heatsink, Black Anodized

Electrical Specifications

Frequency Range, GHz	DC to 6
Impedance, Ohms	50
Attenuation Value, dB	10
Maximum Input Power, Watts	100
Maximum VSWR	1.45:1

Frequency 1

Range, GHz	DC to 2
VSWR	1.2:1
Attenuation Accuracy, dB	± 0.75

Frequency 2

Range, GHz	2 to 4
VSWR	1.35:1
Attenuation Accuracy, dB	± 1

Frequency 3

Range, GHz	4 to 6
VSWR	1.45:1
Attenuation Accuracy, dB	± 1.25

Mechanical Specifications

Temperature

Operating Range, deg C -55 to +125

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 10 dB Fixed Attenuator, N Male To 7/16 DIN Female Directional Rated To 100 Watts Up To 6 GHz PE7205-10

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451 Sales@Pasternack.com • Techsupport@Pasternack.com



10 dB Fixed Attenuator, N Male To 7/16 DIN Female Directional Rated To 100 Watts Up To 6 GHz



TECHNICAL DATA SHEET

PE7205-10

Size

 Length, in [mm]
 4.9 [124.46]

 Width, in [mm]
 3.8 [96.52]

 Height, in [mm]
 2.7 [68.58]

 Weight, lbs [Kg]
 3 [1.36]

Connector 1

Type N Male
Contact Material and Plating Beryllium

Contact Material and Plating

Coupling Nut Material and Plating

Beryllium Copper, Gold

Stainless Steel, Passivated

Stainless Steel, Passivated

Stainless Steel, Passivated

Connector 2

Type 7/16 DIN Female
Contact Material and Plating Brass, Silver
Body Material and Plating Brass, Silver

Compliance Certifications (visit www.Pasternack.com for current document)

RoHS Compliant Yes

Plotted and Other Data

Notes: Values at 25 °C, sea level

URL: http://www.pasternack.com/10db-fixed-n-male-7-16-female-100-watts-attenuator-pe7205-10-p.aspx

10 dB Fixed Attenuator, N Male To 7/16 DIN Female Directional Rated To 100 Watts Up To 6 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal.

PE7205-10 CAD Drawing

10 dB Fixed Attenuator, N Male To 7/16 DIN Female Directional Rated To 100 Watts Up To 6 GHz

