



## 2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru

### TECHNICAL DATA SHEET

PE5CK1016

Pasternack's 2.4mm 50 GHz Vector Network Analyzer (VNA) calibration kit is used to calibrate VNA and associated test setup, thus allowing Vector Error Correction to compensate for systematic errors inherent in the measurement of the device under test (DUT) allowing for precise and accurate characterization of the DUT's performance. The PE5CK1016 SOLT cal kit includes precisely defined male and female coaxial Short Circuits, Open Circuits, Fixed Loads and Through adapters for use during a standard multi-port calibration process. In addition to the calibration standards a fixed torque break-over style torque wrench and a set of open-ended wrenches are included to be used during the mating and demating of calibration components. The electrical behavior of the calibration standards is defined in the cal kit definition files for Keysight, Rohde & Schwarz, and Anritsu instruments, and are also provided in this manual. These files may be obtained by contacting Tech Support or downloaded from the PE5CK1016 product page on Pasternack's web site. It is necessary to follow the VNA manufacturer's instructions to import the cal kit definitions into the instrument.

A properly performed n-port SOL calibration characterizes the performance of the VNA hardware and any other cables or components out to the plane of the calibration. These affects are then removed from subsequent measurements. Calibrations performed using high quality VNA test cables effectively extends the VNA test ports to the end of the Test cables and this allows for greater flexibility when characterizing a product under test. High quality VNA test port cables are designed to optimize the stability of their phase and magnitude response – this allows the calibration to remain valid over flexure, time, and temperature, and over many mate/de-mate cycles.

Available in stock, ship same day!

#### Features

- SOL or SOLT versions available
- Cal kit definition files for Keysight, Rohde & Schwarz, and Anritsu VNAs
- Works with all major VNAs
- Protective wooden case for safe storage of components
- Torque wrench and tools included

#### Applications

- Calibration of Vector Network Analyzers
- Research and development
- Aerospace and defense
- Production test environments

#### Configuration

Connector	2.4mm
Frequency Range	DC to 50 GHz

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru PE5CK1016](#)



## 2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru

### TECHNICAL DATA SHEET

PE5CK1016

#### Electrical Specifications for PE5CK1016 2.4mm Devices

Item	Part Number	Specifications	Frequency (GHz)
Female Termination Male Termination	PE5TR1006 PE5TR1007	1.02 Max VSWR 1.15 Max VSWR	DC to 4 GHz 4 to 50 GHz
Female Short Male Short	PE5SC3010 PE5SC3011	$\pm 2.0^\circ$ deviation from nominal	DC to 50
Female Open Male Open	PE5SC3025 PE5SC3026	$\pm 2.0^\circ$ deviation from nominal	DC to 50
Adapter Thru Female Thru Female to Male Thru Male	PE91408 PE91409 PE91410	1.06 Max VSWR 1.10 Max VSWR 1.15 Max VSWR	DC to 26.5 26.5 to 40 40 to 50
Torque Wrench Open End Wrench Open End Wrench	PE5019-1A PE5TL1001 PE5TL1002	8 in-lbs Torque Setting 1/4" x 5/16" Dimensions 7/16" x 1/2" Dimensions	

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru PE5CK1016](#)



2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru

## PE5SC3010 2.4mm Female Short Specifications



ELECTRICAL		UNIT
Frequency Range	DC to 50	GHz
Phase	DC to 50 GHz $\pm 2.0^\circ$	Max
Offset Impedance	50	$\Omega$
Offset Loss	2.806	G $\Omega$ /s
Electrical Delay	16.929	ns
Inductance	$L0 \times 10^{-12} = 0$	H
	$L1 \times 10^{-24} = 0$	H/Hz
	$L2 \times 10^{-33} = 0$	H/Hz <sup>2</sup>
	$L3 \times 10^{-42} = 0$	H/Hz <sup>3</sup>

MECHANICAL	
Housing	Gold Plated Beryllium Copper
Connector	2.4mm Female
Screw Thread	M7 x .075-6g
Dimensions	0.55 [13.97] $\varnothing$ , 0.82 [20.83] Length
Pin Depth	0.000 - 0.002

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru PE5CK1016](#)



2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru

## PE5SC3011 2.4mm Male Short Specifications



ELECTRICAL		UNIT
Frequency Range	DC to 50	GHz
Phase	DC to 50 GHz    ±2.0°	Max
Offset Impedance	50	Ω
Offset Loss	2.806	GΩ/s
Electrical Delay	16.929	ns
Inductance	$L0 \times 10^{-12} = 0$	H
	$L1 \times 10^{-24} = 0$	H/Hz
	$L2 \times 10^{-33} = 0$	H/Hz <sup>2</sup>
	$L3 \times 10^{-42} = 0$	H/Hz <sup>3</sup>

MECHANICAL	
Housing	Gold Plated Beryllium Copper
Connector	2.4mm Male
Screw Thread	M7 x .075-6g
Dimensions	0.55 [13.97] Ø, 0.797 [20.24] Length
Pin Depth	0.000 - 0.002

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru PE5CK1016](#)



2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru

## PE5SC3025 2.4mm Female Open Specifications



ELECTRICAL		UNIT
Frequency Range	DC to 50	GHz
Phase	DC to 50 GHz    ±2.0°	Max
Offset Impedance	50	Ω
Offset Loss	2.57	GΩ/s
Electrical Delay	14.927	ps
Capacitance	$C0 \times 10^{-15} = 34.0$	F
	$C1 \times 10^{-27} = 60.0$	F/Hz
	$C2 \times 10^{-36} = 8.7$	F/Hz <sup>2</sup>
	$C3 \times 10^{-45} = -0.08$	F/Hz <sup>3</sup>

MECHANICAL	
Housing	Gold Plated Beryllium Copper
Connector	2.4mm Female
Screw Thread	M7 x .078-6g
Dimensions	0.55 [13.97] Ø, 0.92 [23.37] Length
Pin Depth	0.00025 ±0.00015

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru PE5CK1016](#)



2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru

## PE5SC3026 2.4mm Male Open Specifications



ELECTRICAL			UNIT
Frequency Range	DC to 50		GHz
Phase	DC to 50 GHz	±2.0°	Max
Offset Impedance	50		Ω
Offset Loss	2.57		GΩ/s
Electrical Delay	14.927		ps
Capacitance	C0 x 10 <sup>-15</sup> = 36.0		F
	C1 x 10 <sup>-27</sup> = 50.0		F/Hz
	C2 x 10 <sup>-36</sup> = -0.95		F/Hz <sup>2</sup>
	C3 x 10 <sup>-45</sup> = 0.11		F/Hz <sup>3</sup>

MECHANICAL	
Housing	Gold Plated Beryllium Copper
Connector	2.4mm Male
Screw Thread	M7 x .075-6g
Dimensions	0.55 [13.97] Ø, 0.90 [22.78] Length
Pin Depth	0.00025 ±0.00015

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru PE5CK1016](#)



2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru

## PE5TR1006 2.4mm Female Termination Specifications



ELECTRICAL			UNIT
Frequency Range	DC to 50		GHz
VSWR at	DC to 4 GHz	1.02	Max
Frequency Range	4 to 50 GHz	1.15	Max
Impedance	50		$\Omega$
Power Rating	0.5 watt CW 0.25 kW Peak		

MECHANICAL	
Housing	Gold Plated Beryllium Copper
Connector	2.4mm Female
Screw Thread	M7 x 0.075-6g
Dimensions	0.36 [9.14] $\varnothing$ , 1.52 [38.70] Length
Pin Depth	0.0000 - 0.0020

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru PE5CK1016](#)



2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru

## PE5TR1007 2.4mm Male Termination Specifications



ELECTRICAL			UNIT
Frequency Range	DC to 50		GHz
VSWR at	DC to 4 GHz	1.02	Max
Frequency Range	4 to 50 GHz	1.15	Max
Impedance	50		$\Omega$
Power Rating	0.5 watt CW 0.25 kW Peak		

MECHANICAL	
Housing	Gold Plated Beryllium Copper
Connector	2.4mm Male
Screw Thread	M7 x 0.075-6g
Dimensions	0.36 [9.14] $\varnothing$ , 1.48 [37.59] Length
Pin Depth	0.0000 - 0.0020

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru PE5CK1016](#)





2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru

## PE91408 2.4mm Thru Female Specifications



ELECTRICAL			UNIT
Frequency Range	DC to 50		GHz
VSWR at Frequency Range	DC to 26.5 GHz	1.06	Max
	26.5 to 40 GHz	1.1	Max
	40 to 50 GHz	1.15	Max
Impedance	50		$\Omega$
Typical Delay	66.7		ps


MECHANICAL	
Housing	Gold Plated Beryllium Copper
Connector	2.4mm Female to 2.4mm Female
Screw Thread	M7 x 0.75-6g
Dimensions	0.50 [12.7] $\varnothing$ , 0.99 [25.146] Length
Pin Depth	0.0 - 0.0015

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru PE5CK1016](#)



2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru

## PE91409 2.4mm Thru Male Specifications



ELECTRICAL			UNIT
Frequency Range	DC to 50		GHz
VSWR at Frequency Range	DC to 26.5 GHz	1.06	Max
	26.5 to 40 GHz	1.1	Max
	40 to 50 GHz	1.15	Max
Impedance	50		Ω
Typical Delay	66.7		ps

MECHANICAL	
Housing	Gold Plated Beryllium Copper
Connector	2.4mm Male to 2.4mm Male
Screw Thread	M7 x 0.75-6g
Dimensions	0.50 [12.7] Ø, 0.92 [23.368] Length
Pin Depth	0.0 - 0.0015

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru PE5CK1016](#)



2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru

## PE91410 2.4mm Thru Female to Male Specifications



ELECTRICAL			UNIT
Frequency Range	DC to 50		GHz
VSWR at Frequency Range	DC to 26.5 GHz	1.06	Max
	26.5 to 40 GHz	1.1	Max
	40 to 50 GHz	1.15	Max
Impedance	50		$\Omega$
Typical Delay	66.7		ps

MECHANICAL	
Housing	Gold Plated Beryllium Copper
Connector	2.4mm Female to 2.4mm Male
Screw Thread	M7 x 0.75-6g
Dimensions	0.50 [12.7] $\varnothing$ , 0.95 [24.13] Length
Pin Depth	0.0 - 0.0012

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru PE5CK1016](#)



2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru

## General Instructions and Usage Notes

#	Notes
1	Keep provided protective blue caps installed when not in use.
2	Store in climate controlled environment.
3	Always keep connectors clean.
4	Avoid touching the connector interface.
5	Use caution when handling.
6	For female components, do not insert male pin greater than 0.037" [.94 mm]. <b>Failure to comply will result in damage to the female connector.</b>
7	When mating, always ensure that the components to be interconnected remain in a fixed position while rotating <b>only the coupling nut</b> slowly to mate the connectors.
8	When de-mating, always ensure that the interconnected components remain in a fixed position while rotating <b>only the coupling nut</b> slowly to de-mate the connectors.
9	Visually inspect the connector threads prior to use. If needed, clean the center conductor pin and outer conductor with alcohol to remove any debris that may be present. <b>Be sure to apply the alcohol in a circular motion with a lint-free cloth or applicator.</b>
10	Use at room temperature.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru PE5CK1016](#)



## 2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru

### TECHNICAL DATA SHEET

PE5CK1016

(see [product page](#) for current document)

#### Plotted and Other Data

Notes:

- Values at +25 °C, sea level

2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm SOLT VNA Calibration Kit Operating from DC to 50 GHz, Including Short Circuit, Open Circuit, Load, and Thru PE5CK1016](#)

URL: <https://www.pasternack.com/2.4mm-short-open-load-thru-solt-vna-calibration-kit-50ghz-pe5ck1016-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.