

16 dB Fixed Attenuator, 75 Ohm F Male to 75 Ohm F Female Brass Tri-Metal Body Rated to 2 Watts Up to 3 GHz

RF Fixed Attenuators Technical Data Sheet

Features

- DC to 3 GHz Frequency Range
- Attenuation 16±3 dB

Applications

- Instrumentation
- Precision measurements

- Max Power 2 Watts (CW)
- VSWR < 1.3:1
- Prototyping and characterization
- Production systems

Description

Pasternack carries a wide range of fixed attenuators with a broad selection of attenuation levels, frequency ranges, and power dissipation ranges. RF microwave attenuators (also known as RF pads) lower the amplitude of a signal (attenuate) a known amount and can be used in a wide variety of applications. These attenuator pads are used when a signal needs to be reduced to protect measurement equipment or other circuitry, to extend the range of power meters and amplifiers, and to impedance match circuits by reducing the VSWR seen by adjacent components. RF attenuators can prevent signal overload in amplifiers, receivers and detectors, adjusting the signal level to a range that is optimal.

Few RF components are as commonly used as fixed coaxial attenuators, and Pasternack carries one of the largest in-stock varieties and ships them same day. The 16 dB Fixed Attenuator PE7396-16 is rated to 2 Watts and operates from DC to 3 GHz. The versatile coaxial package uses F male to F female connectors and is also REACH and ROHS compliant.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
Impedance		75		Ohms
Nominal Attenuation		16		dB
VSWR			1.3:1	
Input Power, CW			2	Watts

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Range	DC to 2	2 to 3				GHz
Attenuation Accuracy, Typ	±0.5	±3				dB

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 16 dB Fixed Attenuator, 75 Ohm F Male to 75 Ohm F Female Brass Tri-Metal Body Rated to 2 Watts Up to 3 GHz PE7396-16

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





16 dB Fixed Attenuator, 75 Ohm F Male to 75 Ohm F Female Brass Tri-Metal Body Rated to 2 Watts Up to 3 GHz

RF Fixed Attenuators Technical Data Sheet

PADE)-K

PE7396-16

Mechanical Specifications

Size Length Width/Diameter Weight Body Material and Plating

2.02 in [51.31 mm] 0.43 in [10.92 mm] 0.06 lbs [27.22 g] Brass, Tri-Metal

Fixed Connectorized Module

Connectors

Configuration Design

Package Style

Description	Connector 1	Connector 2	
Туре	F Male	F Female	
Contact Material and Plating	Brass, Gold	Phosphor Bronze, Gold	
Contact Plating Specification	4µ-inch min.	4µ-inch min.	
Dielectric Type	Teflon	Teflon	
Coupling Nut Material and Plating	Brass, Tri-Metal		
Hex Size	7/16 in.		
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal	
Body Plating Specification	100µ-inch min.	100µ-inch min.	

Environmental Specifications

Temperature Operating Range

-55 to +80 deg C

Compliance Certifications (visit www.Pasternack.com for current document) RoHS Compliant

12/17/2015

Plotted and Other Data Notes:

REACH Compliant

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 16 dB Fixed Attenuator, 75 Ohm F Male to 75 Ohm F Female Brass Tri-Metal Body Rated to 2 Watts Up to 3 GHz PE7396-16

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



16 dB Fixed Attenuator, 75 Ohm F Male to 75 Ohm F Female Brass Tri-Metal Body Rated to 2 Watts Up to 3 GHz

RF Fixed Attenuators Technical Data Sheet



PE7396-16

16 dB Fixed Attenuator, 75 Ohm F Male to 75 Ohm F Female Brass Tri-Metal Body Rated to 2 Watts Up to 3 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 16 dB Fixed Attenuator, 75 Ohm F Male to 75 Ohm F Female Brass Tri-Metal Body Rated to 2 Watts Up to 3 GHz PE7396-16

URL: http://www.pasternack.com/16db-fixed-f-male-f-female-2-watts-attenuator-pe7396-16-p.aspx

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

PE7396-16 CAD Drawing 16 dB Fixed Attenuator, 75 Ohm F Male to 75 Ohm F Female

Brass Tri-Metal Body Rated to 2 Watts Up to 3 GHz

