



2.4mm Female Shorting Dust Cap With 3.5 Inch Chain

Shorts and Caps Technical Data Sheet

PE6195

Features

- Protects against dust and contaminants
- Protects against physical damage
- Passivated Stainless Steel Body
- Internally Shorted
- Chain Included

Applications

- General Purpose Laboratory Use
- Test and Measurement
- ESD Protection

Description

Pasternack's PE6195 RF connector dust cap has a 2.4mm interface and a female gender. Our 2.4mm female dust cap is a shorting design with a passivated stainless steel body to ensure durability. The Pasternack shorting 2.4mm connector cap comes with a 3.5 inch chain and is part of over 40,000 RF, microwave and millimeter wave products that ship the same day.

RF connector dust caps are essential for precision connectors, protecting them from dust, corrosion and potential damage especially to test and measurement equipment. Specific RF connector cap models come with a chain to prevent loss or misplacement. Internal short connector cap versions are available to protect equipment from a spike in current caused by electrostatic discharge (ESD).

Mechanical Specifications

Configuration

Connector	2.4mm Female Shorting
Chain Option	3.5 in Chain

Description	Material	Plating
Body	Passivated Stainless Steel	
Chain	Stainless Steel	

Size

Length	0.49 in [12.45 mm]
Width	0.23 in [5.84 mm]
Height	0 in [0 mm]
Weight	0.01 lbs [4.54 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm Female Shorting Dust Cap With 3.5 Inch Chain PE6195](#)



2.4mm Female Shorting Dust Cap With 3.5 Inch Chain

Shorts and Caps Technical Data Sheet

PE6195

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

2.4mm Female Shorting Dust Cap With 3.5 Inch Chain from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm Female Shorting Dust Cap With 3.5 Inch Chain PE6195](#)


URL: <https://www.pasternack.com/shorting-2.4mm-female-with-3.5-inch-chain-dust-cap-pe6195-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE6195 CAD Drawing

2.4mm Female Shorting Dust Cap With 3.5 Inch Chain

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
C	PCR PE6195 20211011 Removed Marking	11/17/2021	SRAUTUS



UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

.X = ±.2	[5.08]	FRACTIONS
.XX = ±.02	[.51]	± 1/32
.XXX = ±.005	[.13]	ANGLES ± 1°

CABLE LENGTH (L) TOLERANCES:

L ≤ 12	[305]	= +1 [25] / -0
12 [305] < L ≤ 60	[1524]	= +2 [51] / -0
60 [1524] < L ≤ 120	[3048]	= +4 [102] / -0
120 [3048] < L ≤ 300	[7620]	= +6 [152] / -0
300 [7620] < L		= +5%L / -0

ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.



Pasternack Enterprises, Inc.
P.O. Box 16759, Irvine, CA 92623.
Phone: 1.949.261.1920 | 1.866.727.8376
Fax: 1.949.261.7451
Website: www.pasternack.com
E-mail: sales@pasternack.com

THIRD-ANGLE PROJECTION

THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNAK CORPORATION ALL RIGHTS RESERVED.

SHEET 1 OF 1
SCALE N/A

REV	C
ITEM NO.	PE6195
DRAWN BY	DMAY
SIZE	A
CAGE CODE	53919

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.