

20 dB Fixed Attenuator, SMA Male to SMA Female Directional Black Anodized Aluminum Heatsink Body Rated to 100 Watts Up to 18 GHz



RF Fixed Attenuators Technical Data Sheet

PE7425-20

Features

- Directional
- DC to 18 GHz Frequency Range
- Attenuation 20dB Typical

- Max Power 100 Watts (CW)
- VSWR < 1.35:1

Applications

 Instrumentation//Precision measurements//Prototyping and characterization//Production systems

Description

Pasternack carries a wide range of fixed attenuators with a broad selection of attenuation levels, frequency ranges, and power dissipation ranges. RF microwave attenuators (also known as RF pads) lower the amplitude of a signal (attenuate) a known amount and can be used in a wide variety of applications. These attenuator pads are used when a signal needs to be reduced to protect measurement equipment or other circuitry, to extend the range of power meters and amplifiers, and to impedance match circuits by reducing the VSWR seen by adjacent components. RF attenuators can prevent signal overload in amplifiers, receivers and detectors, adjusting the signal level to a range that is optimal.

Few RF components are as commonly used as fixed coaxial attenuators, and Pasternack carries one of the largest in-stock varieties and ships them same day. The 20 dB Fixed Attenuator PE7425-20 is rated to 100 Watts and operates from DC to 18 GHz. The versatile coaxial package uses SMA male to SMA female connectors and is also REACH and RoHS compliant. The Black Anodized Aluminum Heatsink body allows for efficient heat dissipation under high power usage conditions.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------------------------|----------------------|---------|---------|--------|
| Frequency Range | DC | | 18 | GHz |
| Impedance | | 50 | | Ohms |
| Nominal Attenuation | | 20 | | dB |
| Attenuation Accuracy | | 1 | | dB |
| VSWR | | | 1.35:1 | |
| Input Power, CW | | | 100 | Watts |
| rated at +25°C, derated linea | rly to 10W at +125°C | | | |
| Input Power, Peak | | | 1 | kWatts |
| 5µs pulse, 2.5% duty cycle | | | | |

Electrical Specification Notes: Values at +25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 20 dB Fixed Attenuator, SMA Male to SMA Female Directional Black Anodized Aluminum Heatsink Body Rated to 100 Watts Up to 18 GHz PE7425-20

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



20 dB Fixed Attenuator, SMA Male to SMA Female Directional Black Anodized Aluminum Heatsink Body Rated to 100 Watts Up to 18 GHz



RF Fixed Attenuators Technical Data Sheet

PE7425-20

Mechanical Specifications

Size

 Length
 4.78 in [121.41 mm]

 Width/Diameter
 2.5 in [63.5 mm]

 Weight
 0.8695 lbs [394.4 g]

Body Material and Plating Black Anodized Aluminum Heatsink

Configuration

Design Fixed, Directional
Package Style Connectorized Module

Connectors

| Connector 1 | Connector 2 | |
|----------------------------|--|--|
| SMA Male | SMA Female | |
| MIL-STD-348A | MIL-STD-348A | |
| Beryllium Copper, Gold | Beryllium Copper, Gold | |
| Passivated Stainless Steel | Passivated Stainless Steel | |
| | SMA Male MIL-STD-348A Beryllium Copper, Gold | |

Environmental Specifications

Temperature

Operating Range -55 to +125 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

20 dB Fixed Attenuator, SMA Male to SMA Female Directional Black Anodized Aluminum Heatsink Body Rated to 100 Watts Up to 18 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 20 dB Fixed Attenuator, SMA Male to SMA Female Directional Black Anodized Aluminum Heatsink Body Rated to 100 Watts Up to 18 GHz PE7425-20

URL: https://www.pasternack.com/20db-fixed-sma-male-sma-female-100-watts-attenuator-pe7425-20-p.aspx

PE7425-20 CAD Drawing

20 dB Fixed Attenuator, SMA Male to SMA Female Directional Black Anodized Aluminum Heatsink Body Rated to 100 Watts Up to 18 GHz

