

0 to 99dB Rotary Step Attenuator, SMA Female to SMA Female With 1 dB Step Rated to 2 Watts Up to 8GHz



PE7443-99

Features

- 1 dB steps from 0 to 99 dB Attenuation
- · Rotary Dial Control
- · SMA Female Connectors

Applications

- Instrumentation
- · Precision Measurements

- 0°C to +54°C Operating Temperature
- ±2 dB Typical Attenuation Accuracy
- · Prototyping and Characterization
- Production Systems

Description

The PE7443-99 is a Step Attenuator that has 99 dB of total attenuation with 1 dB step size and rotary dial design across a frequency range from DC to 8 GHz. The design is tried and true technology that offers exceptional performance characteristics that include 1 dB maximum insertion loss, and a maximum VSWR of 1.5:1 at 8 GHz. The design also features excellent attenuation accuracy with ±2 dB typical at 8 GHz. The Aluminum package has SMA Female connectors, and operates within the temperature range of 0°C to 54°C.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		8	GHz
Impedance		50		Ohms
Insertion Loss			1	dB
Attenuation Value		0 to 99		dB
Step Size		1		dB
Step Type		Rotary		
Input Power (CW)			2	Watts
Input Power, Peak			200	Watts
5µs Pulse Width,1% DutyCycle				
VSWR			1.5:1	

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Range	DC to 8					GHz
Attenuation Accuracy	2					dB

Electrical Specification Notes:

Attenuation Accuracy specification is ±3.5% dB typ for any attenuation above 70dB.

Mechanical Specifications

Size

 Length
 6.417 in [162.99 mm]

 Width
 1.772 in [45.01 mm]

 Height
 1.89 in [48.01 mm]

 Weight
 0.05 lbs [22.68 g]



0 to 99dB Rotary Step Attenuator, SMA Female to SMA Female With 1 dB Step Rated to 2 Watts Up to 8GHz



PE7443-99

Connectors

Description	Connector 1	Connector 2	
Туре	SMA Female	SMA Female	
Contact Material and Plating	Beryllium Copper, Gold		
Body Material and Plating	Stainless Steel	Aluminum	

Environmental Specifications

Temperature

Operating Range 0 to 54 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

0 to 99dB Rotary Step Attenuator, SMA Female to SMA Female With 1 dB Step Rated to 2 Watts Up to 8GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 0 to 99dB Rotary Step Attenuator, SMA Female to SMA Female With 1 dB Step Rated to 2 Watts Up to 8GHz PE7443-99

URL: https://www.pasternack.com/99db-step-sma-female-sma-female-2-watts-attenuator-pe7443-99-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. <u>Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.</u>

