

5 Watt RF Load (Termination) Up to 6 GHz With N Male Input Black Anodized Aluminum Body

PE6TR1183

Features

- · DC to 6 GHz Frequency Range
- 50 Ohm Impedance
- N-Type Male Coaxial Interface

Applications

- 5G Cellular Bands
- SatCom
- Radar Systems

- Max VSWR 1.25:1
- Max Power 5 Watts (CW)
- · Test and Measurement
- · Commercial and Military Communication
- · DAS Systems

Description

Pasternack's PE6TR1183 is an RF termination (also called RF load or dummy load) that operates from DC to 6 GHz and handles up to 5 Watt (CW). Our N-type termination / load has a male gender. PE6TR1161 N-type load termination offers 1.25:1 max VSWR.

RF load / terminations are indispensable components in many RF, microwave and millimeter wave systems where signal reflection from unused ports can potentially damage the device or reduce the signal integrity. By using a terminator on an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These termination components are commonly used to terminate devices such as couplers, circulators, and switches. They are also widely used in measurement systems to ensure accurate results. Pasternack offers a huge selection of RF, microwave and millimeter wave terminations up to 65 GHz with excellent performance over the entire operating range and power handling capabilities up to 800 Watt (CW).

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|------------------|---------|---------|---------|-------|
| Frequency Range | DC | | 6 | GHz |
| Impedance | | 50 | | Ohms |
| VSWR, Input | | | 1.25:1 | |
| Input Power (CW) | | | 5 | Watts |

Mechanical Specifications

Size

 Length
 1.472 in [37.39 mm]

 Width
 0.787 in [19.99 mm]

 Height
 0.79 in [20.07 mm]

 Weight
 0.0882 lbs [40.01 g]

 Package Type
 Connectorized

Configuration

Connector N Male

Material Specifications

| Description | Material | Plating |
|------------------|-------------------------|-----------|
| Connector 1 Body | Brass | Tri-Metal |
| Housing | Black Anodized Aluminum | |



5 Watt RF Load (Termination) Up to 6 GHz With N Male Input Black Anodized Aluminum Body



PE6TR1183

Environmental Specifications

Temperature

Operating Range Ingress Protection (IP) Rating -40 to +75 deg C

IP65

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

5 Watt RF Load (Termination) Up to 6 GHz With N Male Input Black Anodized Aluminum Body from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 5 Watt RF Load (Termination) Up to 6 GHz With N Male Input Black Anodized Aluminum Body PE6TR1183

URL: https://www.pasternack.com/5-watts-n-male-rf-load-6-ghz-pe6tr1183-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. <u>Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.</u>

