

15 dB RF fixed attenuator 2W, DC to 6GHz,
SMA Male to SMA Female, Stainless Steel



PE7608-15

Features

- DC to 6 GHz Range
- Attenuation 15 ±0.75 dB
- 2 Watts (CW) Power
- VSWR <1.35:1

Applications

- Precision Measurements
- Production Systems
- Instrumentation
- Prototyping and Characterization

Description

Pasternack carries a wide range of fixed attenuators with a broad selection of attenuation levels, frequency ranges, and power dissipation ranges. RF microwave attenuators (also known as RF pads) lower the amplitude of a signal (attenuate) a known amount and can be used in a wide variety of applications. These attenuators pads are used when a signal needs to be reduced to protect measurement equipment or other circuitry, to extend the range of power meters and amplifiers, and to impedance match circuits by reducing the VSWR seen by adjacent components. RF attenuators can prevent signal overload in amplifiers, receivers and detectors, adjusting the signal level to a range that is optimal.

Few RF components are as commonly used as fixed coaxial attenuators, and Pasternack carries one of the largest in-stock varieties and ships them same day. The 15 dB Fixed Attenuators PE7608-15 is rated to 2 Watts and operates from DC to 6 GHz. The versatile coaxial package uses SMA male to SMA female connectors.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|----------------------|---------|---------|---------|-------|
| Frequency Range | DC | | 6 | GHz |
| Impedance | | 50 | | Ohms |
| Nominal Attenuation | | 15 | | dB |
| Attenuation Accuracy | | 0.75 | | dB |
| VSWR | | | 1.35:1 | |
| Input Power, CW | | | 2 | Watts |

Specifications by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------|---------|--------|----|----|----|-------|
| Frequency Range | DC to 4 | 4 to 6 | | | | GHz |
| VSWR, Max | 1.2:1 | 1.35:1 | | | | |

Mechanical Specifications

Size

| | |
|---------------------------|----------------------------|
| Length | 0.98 in [24.89 mm] |
| Width/Diameter | 0.315 in [8 mm] |
| Height | 0.315 in [8 mm] |
| Weight | 0.01 lbs [4.54 g] |
| Body Material and Plating | Passivated Stainless Steel |

Configuration

| | |
|--------|----------------------|
| Design | Fixed, Bidirectional |
|--------|----------------------|

15 dB RF fixed attenuator 2W, DC to 6GHz,
SMA Male to SMA Female, Stainless Steel



PE7608-15

Connectors

| Description | Connector 1 | Connector 2 |
|------------------------------|----------------------------|----------------------------|
| Type | SMA Male | SMA Female |
| Contact Material and Plating | Beryllium Copper, Gold | Beryllium Copper, Gold |
| Dielectric Type | Teflon | Teflon |
| Body Material and Plating | Passivated Stainless Steel | Passivated Stainless Steel |

Environmental Specifications

Temperature

Operating Range -50 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data

15 dB RF fixed attenuator 2W, DC to 6GHz, SMA Male to SMA Female, Stainless Steel from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [15 dB RF fixed attenuator 2W, DC to 6GHz, SMA Male to SMA Female, Stainless Steel PE7608-15](#)

URL: <https://www.pasternack.com/15db-fixed-sma-male-sma-female-2-watts-attenuator-pe7608-15-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE7608-15 CAD Drawing

15 dB RF fixed attenuator 2W, DC to 6GHz, SMA Male to SMA Female, Stainless Steel

