



Absorptive SPDT PIN Diode Switch Operating from 800 MHz to 2.7 GHz Up to 100 Watts (+50 dBm) and SMA

PIN Diode Switches Technical Data Sheet

PE71S2041

Features

- SPDT PIN Diode Switch
- Terminated
- 800 to 2700 MHz Bandwidth
- Insertion loss: 1.2 dB max
- Isolation: 60 dB min
- 50 Ohms
- Switching Speed: 10 microseconds
- DC voltage: +15 Vdc
- SMA female connectors
- TTL Control Logic

Applications

- Electronic Warfare
- Test & Measurement
- Military and Wireless Communications Systems
- Military & Space Radar

Description

The PE71S2041 is a single pole double throw (SPDT) terminated PIN diode switch that operates over the frequency range of 800 MHz to 2700 MHz. The 50 ohm design supports TTL control logic and is rated up to 100 Watts average RF input power. Typical performance includes 1.2 dB insertion loss and greater than 60 dB isolation. Switching speed is 10 microseconds with 1.4:1 typical VSWR and an operating voltage of +15 Vdc with 80 mA nominal current. The rugged package design supports SMA Female RF input/output connectors. The Switch design is highly reliable with an operational temperature of 0°C to +70°C.

Electrical Specifications

TTL Control

Off/Isolation: "0" 0 to V
On/Low Loss: "1"

Description	Minimum	Typical	Maximum	Units
Frequency Range	0.8		2.7	GHz
Impedance		50		Ohms
VSWR			1.4:1	
Insertion Loss		0.8		dB
Isolation		75		dB
Switching Time		6	10	us
Input Power (CW)			100	Watts
Input Power, Hot Switching (CW)			30	Watts
Positive Operating Voltage		15		Vdc
Current @ 15 Vdc		80		mA
Operating Temperature	0		+70	deg C

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Absorptive SPDT PIN Diode Switch Operating from 800 MHz to 2.7 GHz Up to 100 Watts \(+50 dBm\) and SMA PE71S2041](#)



Absorptive SPDT PIN Diode Switch Operating from 800 MHz to 2.7 GHz Up to 100 Watts (+50 dBm) and SMA

PIN Diode Switches Technical Data Sheet

PE71S2041

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	0.8 to 2	2 to 2.7				GHz
Insertion Loss, Max	1	1.2				dB
Insertion Loss, Typ	0.6	0.8				dB
Isolation, Min	65	60				dB
Isolation, Typ	75	70				dB

Mechanical Specifications

Size

Length 3 in [76.2 mm]
Width 2.75 in [69.85 mm]
Height 1 in [25.4 mm]

Design Absorptive, SPDT
RF Connector SMA Female
TTL Control Connector Solder Pin

Environmental Specifications

Temperature

Operating Range 0 to +70 deg C
Storage Range -55 to +90 deg C

ESD Sensitivity ESD Sensitive Material. Transport material in Approved ESD bags. Handle only in ESD Workstation.



Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Absorptive SPDT PIN Diode Switch Operating from 800 MHz to 2.7 GHz Up to 100 Watts \(+50 dBm\) and SMA PE71S2041](#)




Absorptive SPDT PIN Diode Switch Operating from 800 MHz to 2.7 GHz Up to 100 Watts (+50 dBm) and SMA

PIN Diode Switches Technical Data Sheet

PE71S2041

Typical Performance Data




Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Absorptive SPDT PIN Diode Switch Operating from 800 MHz to 2.7 GHz Up to 100 Watts \(+50 dBm\) and SMA PE71S2041](#)



Absorptive SPDT PIN Diode Switch Operating from 800 MHz to 2.7 GHz Up to 100 Watts (+50 dBm) and SMA

PIN Diode Switches Technical Data Sheet

PE71S2041



Absorptive SPDT PIN Diode Switch Operating from 800 MHz to 2.7 GHz Up to 100 Watts (+50 dBm) and SMA from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Absorptive SPDT PIN Diode Switch Operating from 800 MHz to 2.7 GHz Up to 100 Watts \(+50 dBm\) and SMA PE71S2041](https://www.pasternack.com/absorptive-spdt-pin-diode-switch-2.7-ghz-100-watts-sma-pe71s2041-p.aspx)

URL: <https://www.pasternack.com/absorptive-spdt-pin-diode-switch-2.7-ghz-100-watts-sma-pe71s2041-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE71S2041 CAD Drawing

Absorptive SPDT PIN Diode Switch Operating from 800 MHz to 2.7 GHz Up to 100 Watts (+50 dBm) and SMA



TTL LOW=COMMON TO J1
TTL HIGH=COMMON TO J2

STANDARD TOLERANCES
.XX ±0.010
.XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES



Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com

DWG TITLE

PE71S2041

CAGE CODE 53919

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME
3. DIMENSIONS ARE IN INCHES [mm].

CAD FILE 052917

SCALE N/A

SIZE A

1408