



Electromechanical Relay Switches Technical Data Sheet

PE71S6421

Features

- Single Pole Double Throw Electromechanical Relay Switch
- DC to 26.5 GHz Frequency Range
- Failsafe Actuator
- · 2M Lifecycle Rating
- Insertion Loss 0.35 dB typ
- Isolation > 80 dB typ
- VSWR 1.4:1 typ
- Terminal Solder Pins for DC Control

- +28 Volt DC Bias
- SMA Female Connectors
- -25°C to +65°C Operating Temperature
- Up to 90 Watt Average Power Handling
- 50 Ohm Design
- · Hot Switching Capability Consult Factory
- S-Parameter Data available upon request
- Rugged Design meets Mil-STD-202 Test Conditions

Applications

- Aerospace & Defense
- Test & Measurement
- Microwave Radio Systems
- Military & Commercial Communication Systems
- · Research & Development
- SATCOM

- Wireless Communications
- Enterprise
- IoT

Description

The PE71S6421 is a Single Pole Double Throw (SPDT) electromechanical relay switch that operates across a wide frequency range of DC to 26.5 GHz and can handle up to 90 Watts of CW input power in a break before make condition. The 50 Ohm design features a Failsafe Actuator and is rated for 2 million lifecycles. Impressive typical performance includes 0.35 dB insertion loss and isolation greater than 80 dB. This switch requires +28Vdc bias voltage and operates over a temperature range of -25°C to +65°C. The rugged and compact package assembly supports SMA female connectors and terminal solder pins for DC control. And for highly reliable operation, the model is guaranteed to meet MIL-STD-202 environmental test conditions for shock and random vibration.

Electrical Specifications

Switch Type SPDT
Actuator Type Failsafe

Switching Sequence Break before Make

Description	Minimum	Typical	Maximum	Units	
Frequency Range	DC		26.5	GHz	
Impedance			Ohms		
Operating Voltage	26	26 28 30		Volts	
Actuating Set Current @ 28 Volts At +20°C			90	mA	
VSWR		1.4:1	1.7:1		
Insertion Loss		0.35	0.6	dB	
Isolation	50	80		dB	
Input Power (CW)			90	Watts	

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SPDT Failsafe DC to 26.5 GHz Electro-Mechanical Relay Switch, Up To 90W, 28V, 2M Lifecycles, SMA PE71S6421

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





Electromechanical Relay Switches Technical Data

PE71S6421

Switching Time	20	ms Max

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 6	6 to 12	12 to 18	18 to 26.5		GHz
VSWR, Max	1.2:1	1.3:1	1.4:1	1.7:1		
Insertion Loss, Max	0.15	0.25	0.35	0.6		dB
Isolation, Min	80	70	60	50		dB

Mechanical Specifications

Size

Body Material and Plating
Package Type
Aluminum
Connectorized
Operating Life
2,000,000 Cycles

Connectors

RF Connector Type SMA Female
Control Connector Solder Terminals

Environmental Specifications

Temperature

Operating Range -25 to +65 deg C Storage Range -55 to +100 deg C

Humidity Moisture Resistance

Shock MIL-STD-202 Method 213, Cond. D 500G Non Operat-

ing

Vibration MIL-STD-202 Method 204, Cond. D 10G RMS Non

Operating

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SPDT Failsafe DC to 26.5 GHz Electro-Mechanical Relay Switch, Up To 90W, 28V, 2M Lifecycles, SMA PE71S6421

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com






Electromechanical Relay Switches Technical Data

PE71S6421

Typical Performance Data





Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SPDT Failsafe DC to 26.5 GHz Electro-Mechanical Relay Switch, Up To 90W, 28V, 2M Lifecycles, SMA PE71S6421


Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451





Electromechanical Relay Switches Technical Data

PE71S6421



SPDT Failsafe DC to 26.5 GHz Electro-Mechanical Relay Switch, Up To 90W, 28V, 2M Lifecycles, SMA from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SPDT Failsafe DC to 26.5 GHz Electro-Mechanical Relay Switch, Up To 90W, 28V, 2M Lifecycles, SMA PE71S6421

URL: https://www.pasternack.com/spdt-electromechanical-relay-failsafe-switch-26.5-ghz-90w-28v-sma-pe71s6421-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

PE71S6421 CAD Drawing

SPDT Failsafe DC to 26.5 GHz Electro-Mechanical Relay Switch, Up To 90W, 28V, 2M Lifecycles, SMA

