



Technical Data Sheet

PEWAN137-15NF

Features

- 5.85 GHz to 8.2 GHz
- WR-137 Waveguide Band

- 15 dBi Nominal Gain
- · N Female Connector

Applications

- Antenna Measurements
- · Wireless Communication
- Laboratory Use

- Microwave Radio Systems
- · Radome Testing
- Automotive Antenna Test
- Solutions
- · Radar Cross Section
- Satellite Antenna Testing

Description

The PEWAN137-15NF standard gain horn antenna (also known as waveguide horn) from Pasternack is part of our comprehensive selection of waveguide antennas. This standard gain horn is mated with a WR-137 to N Female waveguide to coaxial adapter and operates from 5.85 GHz to 8.2 GHz.

Our PEWAN137-15NF standard gain horn antenna has a nominal gain of 15 dBi with a Horizontal and Vertical HPBW (Half Power Beam Width) of 31 dB and 32 dB respectively. Pasternack's N Female to WR-137 standard gain horns are available in 10, 15 and 20 dBi models with pyramidal shape and connectorized input.

Waveguide antennas, such as the PEWAN137-15NF are used in a wide variety of applications due to the high-power handling capability, low loss, high directivity, and near constant electrical performance. Our WR-137 waveguide antennas with N Female interface is part of over 40,000 RF, microwave and millimeter wave components from Pasternack available worldwide and Ship same day.

Configuration

Design Coaxial Interface WR-137 Standard Gain Horn N Female

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	5.85		8.2	GHz
Waveguide Standard Gain Horn				
Gain		15		dBi
Horizontal Half Power Beam Width		31		Degrees
Vertical Half Power Beam Width		32		Degrees
Waveguide to Coaxial Adapter				
Input VSWR			1.3:1	

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: WR-137 Standard Gain Horn with 15 dBi gain, N Female connector PEWAN137-15NF

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451





Technical Data Sheet

PEWAN137-15NF

Mechanical Specifications

Size

 Length
 7.004 in [177.9 mm]

 Width
 3.707 in [94.16 mm]

 Height
 2.668 in [67.77 mm]

 Weight
 0.5265 lbs [238.82 g]

RF Connector

Type N Female

Waveguide Interface

Waveguide Size WR-137

Environmental Specifications

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:






Technical Data Sheet

PEWAN137-15NF

Typical Performance Data








Technical Data Sheet

PEWAN137-15NF








Technical Data Sheet

PEWAN137-15NF








Technical Data Sheet

PEWAN137-15NF



WR-137 Standard Gain Horn with 15 dBi gain, N Female connector from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: WR-137 Standard Gain Horn with 15 dBi gain, N Female connector PEWAN137-15NF

URL:

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PEWAN137-15NF CAD DrawingWR-137 Standard Gain Horn with 15 dBi gain, N Female connector

