

Low PIM NEX10 Male to NEX10 Male Adapter



PE91713

Configuration

- NEX10 Male Connector 1
- NEX10 Male Connector 2
- 50 Ohm
- Low PIM Design
- Straight Body Geometry

Features

- Typical PIM levels of -160 dBc
- Silver Plated Brass Contact
- Max of VSWR 1.15:1 at 3GHz, Max of VSWR 1.25:1 at 6GHz

Applications

- General Purpose Test
- Low PIM Applications

Description

Pasternack's PE91713 NEX10 male to NEX10 male adapter is part of our full line of RF components available for same-day shipping. Our NEX10 to NEX10 adapter has a male to male gender configuration in a low PIM design. PE91713 NEX10 male to NEX10 male adapter operates to 8 GHz. The Pasternack adapter provides a passive intermodulation of -160 dBc typical.

RF adapters are often used to enable connections between two connector types that would otherwise not mate. Certain adapter configurations can also be used to protect connectors on expensive equipment where the number of connect/disconnect cycles is high. An RF, microwave or millimeter wave adapter is connected to the equipment, and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Pasternack also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		8	GHz
Impedance		50 Ohm		
Passive Intermodulation		-160		dBc
Dielectric Withstanding Voltage (AC)			750	Vrms

Mechanical Specifications

Size

Length	1.24 in [31.50 mm]
Width	0.48 in [12.19 mm]
Height	0.48 in [12.19 mm]
Weight	0.04 lbs [16.78 g]

Description	Connector 1	Connector 2
Type	NEX10 Male	NEX10 Male
Polarity	Standard	Standard

Low PIM NEX10 Male to NEX10 Male Adapter



PE91713

Material Specifications

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Type	NEX10 Male		NEX10 Male	
Contact	Brass	Silver	Brass	Silver
Insulation	PTFE		PTFE	
Body	Brass	Tri-Metal	Brass	Tri-Metal
Coupling Nut	Brass	Tri-Metal	Brass	Tri-Metal

Environmental Specifications

Temperature

Operating Range -40 to +155 °C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Low PIM NEX10 Male to NEX10 Male Adapter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Low PIM NEX10 Male to NEX10 Male Adapter PE91713](#)

URL: <https://www.pasternack.com/low-pim-nex10-male-to-nex10-male-adapter-pe91713-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE91713 CAD Drawing

Low PIM NEX10 Male to NEX10 Male Adapter

