

902 to 928 MHz, RFID Flat Panel Antenna, 1.5 dBi Gain, Type N Male, EVA Radome, RHCP

## Antennas Technical Data Sheet

**PEANFP1065**

### Features

- High Performance Multi-tag read/write Capabilities
- Lightweight, Concealable Design
- Right Hand Circular Polarized
- 902 to 928 MHz Frequency Range
- 2 Meter Cable
- Type N Male Connector

### Applications

- Radio Frequency Identification
- Inventory Management
- Access Control
- Data Collection
- Asset Tracking
- Livestock Management

### Description

Pasternack's PEANFP1065 is a RHCP RFID flat panel antenna. The PEANFP1065 with a 1.5 dBi gain nominal is a Directional antenna. Our 902 to 928 MHz antenna has N Male connector.

With an impedance of 50 Ohms and max input power of 20 Watts, the PEANFP1065 flat panel RHCP antenna is well suited for Radio Frequency Identification tag reading applications. This 902-928 MHz 1.5 dBi gain RFID antenna is highly directional providing the reader radio the capabilities of simultaneously reading a multitude of RFID tags with a high degree of accuracy.

Pasternack's RFID PEANFP1065 has a radome made of EVA in Black color and comes from a facility certified to ISO 9001:2015. This N Male connectized Antenna has an overall length of 11 in, width of 5 in, and weighs 0.2866 lbs. Use our on-line ordering system to purchase your PEANFP1065 RFID Directional RHCP antenna 24 hours a day with same-day shipping and no MOQs (minimum order quantities).


### Configuration

Design	Flat Panel
Application Band	RFID
Band Type	Single
Radiation Pattern	Directional
Polarization	RHCP
Cable Type	RG316
Connector Type	N Male
Lightning Protection	DC Grounded

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	902		928	MHz
Input VSWR			1.5:1	
Impedance		50		Ohms
Gain		1.5		dBi
Front to Back Ratio		20		dB
Horizontal (Azimuth) Beam Width		100		Degrees
Vertical (Elevation) Beam Width		58		Degrees
Input Power			20	Watts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [902 to 928 MHz, RFID Flat Panel Antenna, 1.5 dBi Gain, Type N Male, EVA Radome, RHCP PEANFP1065](#)



902 to 928 MHz, RFID Flat Panel Antenna, 1.5 dBi Gain, Type N Male, EVA Radome, RHCP

## Antennas Technical Data Sheet

**PEANFP1065**

### Mechanical Specifications

Radome Material	EVA
<b>Size</b>	
Overall Length	11 in [279.4 mm]
Width	5 in [127 mm]
Height	0.19 in [4.83 mm]
Weight	0.2866 lbs [130 g]

### Connectors

Description	Connector 1	Connector 2	Connector 3
Body Material and Plating	Brass, Nickel		

### Environmental Specifications

<b>Temperature</b>	
Operating Range	-20 to +65 deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

902 to 928 MHz, RFID Flat Panel Antenna, 1.5 dBi Gain, Type N Male, EVA Radome, RHCP from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [902 to 928 MHz, RFID Flat Panel Antenna, 1.5 dBi Gain, Type N Male, EVA Radome, RHCP PEANFP1065](#)

URL: <https://www.pasternack.com/1.5-dbi-flat-panel-antenna-902-928-mhz-n-type-male-connector-peanfp1065-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PEANFP1065 CAD Drawing

902 to 928 MHz, RFID Flat Panel Antenna, 1.5 dBi Gain, Type N Male, EVA Radome, RHCP



REVISION		DESCRIPTION	DATE	CHANGED BY	APPROVED BY
ZONE	REV.	INITIAL RELEASE	02/01/2023	PSRINIVAS	KHIETPAS
	A				

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS
TOLERANCES:
X = ±.2 [5]   FRACTIONS ±.02 [.5]   ±.132
XXX = ±.005 [.13]   ANGLES ± 1°
CABLE LENGTH TOLERANCES:
>12 [305] = +1 [25] / -0
>12 [305] ≤ 60 [1524] = +2 [51] / -0
>60 [1524] ≤ 120 [3048] = +4 [102] / -0
>120 [3048] ≤ 300 [7620] = +6 [152] / -0
>300 [7620] = +5% / -0
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE

NOTES:  
 1. LABEL PER ILS-100-03 (FOR INTERNAL USE ONLY). LABEL LOCATION SHOWN IS FOR REFERENCE ONLY.

REGULATORY COMPLIANCE:  
 EU ROHS DIRECTIVE (MOST RECENT RELEASED VERSION)  
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.  
 THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

PEARN

Website: www.Pasternack.com  
 Phone: 1.866.727.8376 | 1.949.261.1920

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5  
 SCALE NONE  
 SHEET 1 OF 1

DESCRIPTION  
 RFID ANTENNA 902-928MHZ, RHCP, 3.5 dBi, Black EVA, N Male, 1'x5' in

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	53919	PSRINIVAS	PEANFP1065	A